

# Inflator XGT®

## MP001GZ02

40Vmax • 11,1 bar • 161 psi



### Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Maximum Flow Rate	24 L/min
Max Pressure	11,1 bar
Sound Pressure Level (L <sub>pA</sub> )	74 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	3,8 m/s <sup>2</sup>
Vibration Uncertainty (K Factor)	1,5 m/s <sup>2</sup>
Product net weight	2,2 kg
Tool weight with battery	2,9 - 4,1 kg
Product Dimensions (L x W x H):	329 x 108 x 231 mm
Hose length	0,65 m

### User benefits

- Excess air can be released by pressing and holding the air release button
- The machine stops automatically when target pressure is reached
- 3 Inflation modes (High speed, Low speed or Ball modes)
- The machine remembers the pressure setting last time you power off
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- LED job light for easy operation in the dark
- Thermostat protects the machine from overheating
- Ergonomic soft grip handle provides increased comfort
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Increased air discharge amount drastically shortens the time to inflate large tyres of tractors, trucks, and more
- Digital pressure gauge with backlight for increased







**EAN 0197050000293**

Link to product - [www.makitauk.com](http://www.makitauk.com)










# Related products

## Standard AC

821552-6 Makpac case (4)		835U76-2 MakPac Inlay	
TE00000333 Swim Ring Adapter		TE00000334 French Adapter	
TE00000346 Dunlop Adapter		TE00000597 British Adapter	

## Optional AC

TE00000333 Swim Ring Adapter		TE00000334 French Adapter	
TE00000346 Dunlop Adapter		TE00000592 Ball Adapter	
TE00000594 French Adapter		TE00000691 Air Valve Adapter 30 Degree Head	
TE00000796 Air Valve Adapter Head 0°			

## Other

User manual

Parts drawing