

## Combi Drill XGT®

### HP001GZ01

40V max • 140 Nm • 0 – 2 600 min<sup>-1</sup>

**Rugged, brushless combi drill for heavy-duty screwdriving and drilling**

A powerful, brushless drill for screwdriving and drilling with or without hammer action, two power settings. A high maximum torque of 140 / 68 Nm. An ideal choice for jobs that require high power and torque. Integrated LED light. Tool only, battery and charger not included. Tool comes in a Makpac case.



#### Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 650 / 2600 min <sup>-1</sup>
Max. fastening torque Hard/Soft	140 / 68 Nm
Torque setting	41 / 21
Max Torque	150 Nm
Impacts per Minute (IPM)	0 - 9750 / 39000 min <sup>-1</sup>
Drilling Capacity Wood (Auger Bit)	50 mm
Drilling Capacity Wood (Self-feed bit)	76 mm
Max. Drilling Diameter in Masonry	20 mm
Max. Drilling Diameter in Steel	20 mm
Drilling Capacity Flat bit	40 mm
Drilling Capacity Hole Saw	152 mm
Driving Shank	1/2"-20UNF "
Drill Chuck Capacity	1,5 - 13 mm

#### User benefits

- Jog selector for easy adjustment of mounting torque, visual confirmation of the selected torque on the digital display
- Battery protection system automatically shuts off power when the battery level is low
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops









**EAN 0088381894043**

Link to product - [www.makita.uk.com](http://www.makita.uk.com)









# Related products

## Standard AC

<b>127551-9</b> Grip Assembly		<b>122576-8</b> Stopper Pole	
<b>346317-0</b> Belt Hook		<b>784637-8</b> Screw Bit, Ph2 – S6, 45 Mm, Double	
<b>452947-8</b> Bitholder		<b>251314-2</b> Truss Head Screw M4*12, Td140D	
<b>821551-8</b> Makpac case (3)		<b>835F93-2</b> Inner tray (3)	

## Optional AC

<b>122576-8</b> Stopper Pole		<b>127551-9</b> Grip Assembly	
<b>346317-0</b> Belt Hook		<b>452947-8</b> Bitholder	
<b>763252-1</b> Keyless Drill Chuck		<b>784637-8</b> Screw Bit, Ph2 – S6, 45 Mm, Double	

## Other

User manual

Parts drawing