



# 40VMax Router XGT®, RP001GZ02

1/2"



## Technical specifications

|                                                          |                                |
|----------------------------------------------------------|--------------------------------|
| Voltage XGT                                              | ✓                              |
| Nominal Battery Voltage                                  | 40 V                           |
| Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)               | Li-ion                         |
| No load speed                                            | 8000 - 25000 min <sup>-1</sup> |
| Max. Collet Capacity                                     | 1/4, 3/8, 1/2 "                |
| Plunge capacity                                          | 0 - 60 mm                      |
| AWS ready                                                | ✓                              |
| Sound Power Level (L <sub>WA</sub> )                     | 100 dB(A)                      |
| Sound Pressure Level (L <sub>pA</sub> )                  | 92 dB(A)                       |
| Noise Uncertainty (K Factor)                             | 3 dB(A)                        |
| Vibration Level, Cutting Grooves in MDF                  | 6,3 m/s <sup>2</sup>           |
| Vibration Uncertainty (K Factor), Cutting Grooves in MDF | 1,5 m/s <sup>2</sup>           |
| Product net weight                                       | 3,3 kg                         |
| Tool weight with battery                                 | 4,0 - 5,2 kg                   |

**EAN 0197050005427**

Link to product - [www.makitauk.com](http://www.makitauk.com)

## User benefits

- Soft start for smooth start-ups
- Anti-restart function minimises accidental start-up
- Variable speed control dial enables user to match the speed to the application for greater versatility



# Related products

Standard AC

122850-4

Dust Nozzle



122G61-3

Holder Assembly



1914M8-1

ACCESSORY SET

256861-8 (2x)

Rod 8



342428-9

Straight Guide



4130A9-4

Chip Deflector

821552-6

Makpac case (4)



Other

User manual

Parts drawing