

Trimmer XGT®

RT001GZ21

40Vmax • 6 mm / 8 mm • 10 000 - 31 000 min⁻¹

Powerful XGT® 40Vmax brushless trimmer for carpentry

A carpenter's tool that you can use to cut grooves or decorative trimmings in wood. Soft brakes prevent work material from damage. Create dust free working space Auto-start Wireless System (AWS) connects to compatible vacuum cleaner with Bluetooth.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	10000 - 31000 min ⁻¹
Max. Collet Capacity	0 - 1-3/8 "
Plunge capacity	0 - 40 mm
Plunge capacity with trimmer base	0 - 40 mm
Plunge capacity with plunge base	0 - 35 mm
Collet Capacity	6 / 8 mm
AWS ready	✓
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Rotation Without Load	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor),	1,5 m/s ²

User benefits

- Variable speed
- Brushless maintenance-free and long-life motor
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Soft start for smooth start-ups
- Battery protection system automatically shuts off power when the battery level is low
- Constant speed control maintains constant speed under load

EAN 0088381759830

Link to product - www.makita.uk.com



Related products

Standard AC

122703-7

Trimmer Guide Assembly



122965-7

Straight guide assembly



191W55-5

Accessory Set

195559-1

Dust Nozzle



343577-5

Template Guide 8 x 10 x 9.5 mm



781039-9

Wrench 13



821552-6

Makpac case (4)



Optional AC

122703-7

Trimmer Guide Assembly



122965-7

Straight guide assembly



126786-9

Tilt Base Assembly

153489-2

Grip complete 125 mm



194579-2

Guide rail adapter



194733-8

Dust nozzle set Ø 32 / 37 mm



195559-1

Dust Nozzle



195564-8

Guide Holder Set



343577-5

Template Guide 8 x 10 x 9.5 mm



344364-5

Template Guide 14.5 x 16 x 13 mm



763618-5

Collet cone 8 mm



763619-3

Collet Cone 3/8"



781011-1

Wrench 22 mm



781039-9

Wrench 13



821552-6

Makpac case (4)



Other

User manual

Parts drawing