

Jigsaw XGT®

JV002GZ01

40Vmax, 0 - 3 500 min⁻¹

Model JV002G is a cordless jig saw powered by 40Vmax XGT® Li-Ion battery



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	0 - 3500 min ⁻¹
Length of Stroke	26 mm
Max. Bevel Range (Left)	0 - 45 °
Max. Bevel Range (Right)	0 - 45 °
Capacity Aluminium	20 mm
Max. Cutting Capacity in Wood (90°)	135 mm
Max. Cutting Capacity in Steel (90°)	10 mm
Orbital Action	✓
Electronic brake	✓
Sound Power Level (L _{WA})	96 dB(A)
Vibration Level, Cutting Sheet Metal	4,2 m/s ²
Sound Pressure Level (L _{pA})	88 dB(A)

User benefits

- Variable speed control dial enables user to match the speed to the application for greater versatility
- Brushless maintenance-free and long-life motor
- 3 orbital settings

EAN 0197050002037

Link to product - www.makita.uk.com



Related products

Standard AC

122C71-6
Dust Nozzle Assembly



415524-7
Anti-splintering device



783202-0
Hex Wrench 4Mm



821551-8
Makpac case (3)



A-85628
Jig Saw Blade 105 x 1,25 mm



A-85737
Jig Saw Blade 75 x 0,9 mm



A-85793
Jig Saw Blade 105 x 1,25 mm



Optional AC

8359Y2-4
Inner Tray



Other

User manual

Parts drawing