

HLS28XW285XM W/15-813142

► HLS28 HAZARDOUS ENCLOSURE LED STRIP LIGHT



HLS28 Hazardous Enclosure Strip Light; Motion;
Clear Window; 285 mm
12-30 V dc; IP50
Color:White
5 m (15 ft) Integral Cable; SMBWLS28SP bracket
Part Number: 813142

CERTIFICATIONS



SPECIFICATIONS

Power	DC
Cable Length (m)	4.5
IP Rating	IP50
Display	No
Supply Voltage	12-30 V dc
Housing Style	Linear Strip
Primary Housing Material	Aluminum
Illumination	Yes
Mounting Thread	No Thread
Color Input Control	Individual (One wire/color, same number of colors as input wires)

Number of Colors	1
Product Size (mm)	28
Color Technology	Standard LED
Color Option 1	Cool White
Animation Option 1	Solid On
Connection	Cable
Lumens Color 1	800
Color 1 - Wavelength/Color Temp/Coordinates	6500K (Cool)
Max Current Color (mA)	800
Number of Input Pins/Conductors	3
Illuminated Length (LxWxH mm)	285.0
Physical Dimensions (LxWxH or DxH mm)	354.5 x 28.0 x 35.9
Environmental Rating	IP50
High Temperature (up to 100° C)	60
Min Op. Temperature (°C)	-20
Storage Temp (°C)	-40 to 70
Primary Window Material	Polycarbonate Clear
Illumination Switch Function	Motion Activated
Feature: Hazardous Area	Yes
Feature: Audible	No

COMPATIBLE PRODUCTS

BRACKETS

	SMBWLS28RA
Bracket: Right Hand Mounting (Set of Two) hardware included Used with WLS28 models	
	SMBWLS28SM
Bracket: Right angle for Surface Mounting (Set of Two) hardware included Used with WLS28 models	
	SMBWLS28SP
Bracket: For use with WLS28 Set of two snap brackets 300 Series Stainless Steel	
	SMBWLSMAG
Accessory: Magnet Mount Kit; Set of 2 For Use With WLS28 Series Lights 2.3 in Diameter Up to 35 lb Pull	
	SMBWLSMAGR
Accessory: Silicone Magnet Cover Kit For Use With SMBWLSMAG Prevents Scratches on Painted Surfaces	
	SMH1316
Accessory: Mounting Hardware - 13/16 Unistrut Channel	