



2 Piece Combo Kit LXT®

DLX2131TJ

18V

Includes : DHP482 Combi Drill and DTD152 Impact Driver



Models in kit



Combi Drill LXT®
DHP482



Impact Driver LXT®
DTD152



Combi Drill LXT®

DHP482

18V • 62 Nm • 0 – 1 900 min⁻¹

Powerful general-use combi drill with hammer action for professionals

An efficient drill for professional screwdriving and drilling with or without hammer action, two power settings. Max. torque of 62 / 36 Nm. A versatile tool for fitters, builders and maintenance staff. Integrated LED light.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 600 / 1900 min ⁻¹
Max. fastening torque Hard/Soft	62 / 36 Nm
Max Torque	64 Nm
Torque setting	21
Impacts per Minute (IPM)	0 - 9000 / 28500 min ⁻¹
Max. Drilling Diameter in Masonry	13 mm
Max. Drilling Diameter in Concrete	13 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	51 mm
Drilling Capacity Flat bit	38 mm
Drilling Capacity Hole Saw	51 mm
Driving Shank	1/2"-20UNF "

User benefits

- Highly efficient and compact machine for professional use
- Battery protection system automatically shuts off power when the battery level is low
- Optimal handle design
- LED light illuminates the work site
- Ergonomic handle for easy manoeuvring

Link to product - www.makitauk.com



Impact Driver LXT®

DTD152

18V • 1/4" • 165 Nm • 0 – 2 900 min⁻¹

Compact impact driver for quick driving

A compact and light impact wrench with a hex. 1/4" drive shank. A small and light tool that is easy to use but offers a max. fastening torque of 165 Nm, suitable for quick driving. A handy LED light for added lighting.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 2900 min ⁻¹
Max Fastening Torque Impact Drill	165 Nm
Impacts per Minute (IPM)	0 - 3500 min ⁻¹
Tightening Capacity Standard Bolt	M5 - M16
Driving Shank	1/4 "
Sound Power Level (L _{WA})	104 dB(A)
Sound Pressure Level (L _{pA})	93 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of the Tool	10,5 m/s ²
Vibration Uncertainty (K Factor),	1,5 m/s ²

User benefits






- The rubber coating on the handle ensures a firm working grip
- LED light illuminates the work site
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- The screw tip is securely held in place by a quick lateral stroke
- Quick mount for 1/4 "screwdriver
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.com



Related products kit

Standard AC

821551-8 Makpac case (3)		251314-2 Truss Head Screw M4*12, Td140D	
266622-8 Truss Head Screw M4 X 12		346317-0 (2x) Belt Hook	
784637-8 Screw Bit, Ph2 – S6, 45 Mm, Double			

Standard MA

BL1850B (2x) Battery LXT® 5,0 Ah		DC18RC Battery Charger LXT®	
-------------------------------------	---	--------------------------------	---

Optional AC

821551-8 Makpac case (3)	
-----------------------------	---

Other - DHP482

User manual

Parts drawing

Other - DTD152

User manual

Parts drawing