

Impact Wrench LXT®

DTW300

18V • 1/2" • 330 Nm • 0 – 3 200 min⁻¹

Extra-compact and efficient brushless impact wrench with three power settings

Powerful and extra-compact, 144 mm-long, 1/2" drive impact wrench. Small size and light weight make this tool easy to use, while offering a max. fastening torque of 330 Nm. Four power settings. A handy LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max Fastening Torque Impact Drill	100 / 160 / 210 / 330 Nm
No load speed	0 - 1000 / 1800 / 2600 / 3200 min ⁻¹
Impacts per Minute (IPM)	0 - 1800 / 2600 / 3400 / 4000 min ⁻¹
Drive Square	1/2 "
Tightening Capacity Standard Bolt	M10 - M20
Tightening Capacity High Tensile Bolt	M10 - M16
Sound Power Level (L _{WA})	108 dB(A)
Sound Pressure Level (L _{pA})	97 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,5 - 1,8 kg
Product Dimensions (L x W x H):	144 x 81 x 246 mm

User benefits

- Extremely compact thanks to a brushless motor
- Low power consumption thanks to brushless motor
- The narrow design of the handle ensures excellent handling
- Battery protection system automatically shuts off power when the battery level is low
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- 3 modes of reaction time for automatic stop available both in forward and reverse rotation modes

Link to product - www.makita.uk.com



Related products

Optional AC

134874-8

Extension bar 1/2", 100 mm

821550-0

Makpac case (2)

837670-0

MakPac (2) Inlay

B-40222

Impact Socket 1/2" 27 X 42 mm

E-12354

Impact deep socket set, 3 pcs



134877-2
Universal Joint 84 mm



835L10-8
Makpac Type 2 Inner tray (2)



B-40185
Impact Socket 1/2" 21 X 38 mm



B-40238
Impact Socket 1/2" 30 X 44 mm



Other

User manual

Parts drawing