

Impact Wrench LXT®

DTW1002Z

18V • 1/2" • 1 000 Nm • 0 – 1 800 min⁻¹

High-torque, brushless impact wrench with three power settings for heavy-duty use

A powerful, brushless 1/2" drive impact wrench with a fastening torque of up to 1 000 Nm. Three different power settings. Equipped with an LED light for added lighting, this tool is ideal for applications that require high fastening torque. Tool only, battery and charger not included.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
No load speed	0 - 900 / 1000 / 1800 min ⁻¹
Max Fastening Torque Impact Drill	300 / 600 / 1200 Nm
Nut-busting torque	1600 Nm
Tightening Capacity Standard Bolt	M12 - M30
Impacts per Minute (IPM)	0 - 1800 / 2000 / 2200 min ⁻¹
Drive Square	1/2 "
Sound Power Level (L _{WA})	108 dB(A)
Sound Pressure Level (L _{pA})	97 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of	18,0 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- LED light illuminates the work site
- Wide hanging hook, e.g. for scaffolding
- Electric brake for maximum productivity and increased operator safety
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381803397

Link to product - www.makita.com



Related products

Standard AC

251314-2 (2x)
Truss Head Screw M4*12, Td140D



346949-3
Hook



Optional AC

134874-8
Extension bar 1/2", 100 mm



134877-2
Universal Joint 84 mm



191667-2
Extension handle



251314-2 (2x)
Truss Head Screw M4*12, Td140D



346949-3
Hook



821551-8
Makpac case (3)



837645-9
MakPac (3) Inlay



B-40076
Impact Socket 1/2", 8 X 38 mm



B-40185
Impact Socket 1/2" 21 X 38 mm



B-40222
Impact Socket 1/2" 27 X 42 mm



B-40238
Impact Socket 1/2" 30 X 44 mm



B-68448
Bit adapter, 51 mm



E-12354
Impact deep socket set, 3 pcs



Other

User manual

Parts drawing