



2PC Brushless Combo Kit LXT®

DLX2507TJ

18V

Includes DHP489Z 18V Brushless Combi Drill and DTD153Z 18V Brushless Impact Driver



Models in kit



Hammer Driver Drill LXT®
DHP489



Impact Driver LXT®
DTD153

Hammer Driver Drill LXT®

DHP489

18v, 0 – 1 800 min⁻¹, 620 W

Model DHP489 is cordless hammer driver drill powered by 18V LXT® Li-Ion battery

The main features and benefits are: •Excellent drilling capacity: Achieve exceptional drilling capacity, effortlessly tackling 2x lumber with up to 1" ship auger bit in high speed mode •Robust keyless drill chuck with single metal sleeve •Metal gear housing



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 550 / 1800 min ⁻¹
Max. fastening torque Hard/Soft	73 / 40 Nm
Max Torque	110 Nm
Torque setting	21
Impacts per Minute (IPM)	0 - 8250 / 27000 min ⁻¹
Max. Drilling Diameter in Masonry	16 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	51 mm
Drilling Capacity Flat bit	38 mm
Drilling Capacity Hole Saw	51 mm
Driving Shank	1/2"-20UNF "

User benefits

- Built-in LED light with pre-glow and afterglow functions illuminates the work area
- Battery protection system automatically shuts off power when the battery level is low
- Single sleeve keyless chuck enables easy bit installation/removal with one hand
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Electric brake for maximum productivity and increased operator safety
- Reversing switch is conveniently located
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.uk.com



Impact Driver LXT®

DTD153

18V • 1/4" • 170 Nm • 0 – 3 400 min⁻¹

Extra-compact brushless impact driver for quick driving

A compact and light brushless impact driver with a hex. 1/4" drive shank. A small and light tool that is easy to use but offers a max. fastening torque of 170 Nm, suitable for quick driving. A handy LED light for added lighting.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 3400 min ⁻¹
Max Fastening Torque Impact Drill	170 Nm
Impacts per Minute (IPM)	0 - 3600 min ⁻¹
Tightening Capacity Standard Bolt	M5 - M16
Driving Shank	1/4 "
Sound Power Level (L _{WA})	107 dB(A)
Sound Pressure Level (L _{pA})	96 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of the Tool	13,0 m/s ²

User benefits

- Low power consumption thanks to brushless motor
- The rubber coating on the handle ensures a firm working grip
- The screw tip is securely held in place by a quick lateral stroke
- LED light illuminates the work site
- Quick mount for 1/4 "screwdriver
- Battery protection system automatically shuts off power when the battery level is low
- Variable speed control dial enables user to match the speed to the application for greater versatility

Link to product - www.makitauk.com



Related products kit

Standard AC

821551-8
Makpac case (3)



Standard MA

BL1850B (2x)
Battery LXT® 5,0 Ah



Optional AC

194250-8
Adaptor Chuck - 1/4 Hex Keyless



821551-8
Makpac case (3)



821550-0
Makpac case (2)



837670-0
MakPac (2) Inlay



Other - DHP489

User manual

Parts drawing

Other - DTD153

User manual

Parts drawing