

HP 255 15.6 inch G10 Notebook PC (B39RBAT)



Powered for business

The HP 255 G10 Laptop provides essential business-ready features in a thin and light design that's easy to take everywhere you go. The 15.6-inch diagonal display with 85 percent screen-to-body ratio[5], robust AMD Ryzen™ processor[2], fast memory, and storage is powered for productivity, while the included ports connect your peripherals—all at a price you can value.



Nice and light

The HP 255 Laptop keeps up with hybrid workstyles with a thin and light design and 85 percent screen-to-body-ratio.[5]

Built for work and ready for fun

Complete projects with a robust AMD Ryzen™ processor[2], fast memory, SD card reader, and storage.

Be seen and heard with clarity

Effectively collaborate with an integrated camera and AI-based noise reduction with dual-array mics.

Featuring

Let nothing stand in your way

Power through your day with Windows 11 Home and the powerful collaboration and connectivity features from HP. ^[1]

Fast and efficient wireless LAN

The portability of your PC and the reliability of a fast connection determines where you can work. Get a fast and reliable connection in dense wireless environments with gigabit-speed Wi-Fi 6. ^[3]

Be your best virtual self

Sometimes in life, only a face-to-face conversation will do. Thanks to the HP HD camera with wide dynamic range (WDR), you always come off looking your best during virtual conferences in bright and low light conditions.

Protection for minor spills

Help protect sensitive electronics and key components from minor spills with the spill-resistant keyboard.

Specifications

Operating system	Windows 11 Home – HP recommends Windows 11 Pro for business
Product color	Dark ash silver
Processor family	AMD Ryzen™ 3 processor
Processor	AMD Ryzen™ 3 7330U (up to 4.3 GHz max boost clock, 8 MB L3 cache, 4 cores, 8 threads) ^[6,7]
Memory	8 GB DDR4-3200 MT/s (1 x 8 GB)
Memory Slots	2 SODIMM
Internal Storage	256 GB PCIe® NVMe™ SSD
Graphics	Integrated
Graphics (integrated)	AMD Radeon™ Graphics
Display	39.6 cm (15.6") diagonal, FHD (1920 x 1080), narrow bezel, anti-glare, 250 nits, 45% NTSC
Display	15.6" diagonal, FHD (1920 x 1080), narrow bezel, anti-glare, 250 nits, 45% NTSC ^[12,13,14]
Display size (diagonal)	39.6 cm (15.6")
Display size (diagonal)	15.6"
Audio	Stereo speakers, integrated digital microphone
Dimensions (W x D x H)	36 x 23.6 x 1.86 cm
Weight	Starting at 1.52 kg (Weight will vary by configuration. Does not include power adapter.)
Keyboard	Spill-resistant, full-size keyboard with numeric keypad
Pointing device	Touchpad with multi-touch gesture support
Camera	720p HD camera
Ports	1 USB Type-C® 5Gbps signaling rate; 2 USB Type-A 5Gbps signaling rate; 1 AC power; 1 HDMI 1.4b; 1 stereo headphone/microphone combo jack (HDMI cable sold separately.)
Wireless	Realtek Wi-Fi 6 RTL8852BE (2x2) and Bluetooth® 5.3 wireless card
Power	HP Smart 45 W External AC power adapter ^[19]
Battery type	HP Long Life 3-cell, 41 Wh Li-ion
Battery weight	180 g
Energy star certified	ENERGY STAR® certified
Management features	HP SSRM; Windows Push Button Reset Recovery
Sustainable impact specifications	Low Halogen; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; Recycled Plastic cushions; 2% post-consumer recycled plastic
Security management	McAfee Security (30 days free trial) ^[17]
Software included	HP QuickDrop; Dropbox Promotion; HP Smart Health; Express VPN; E-QR Code; sMedio True DVD for HP; Amazon offers; Adobe offer ^[15,16]
UPC number	199251373725
Manufacturer Warranty	1-year and 3-year limited warranties and 90 day software limited warranty options depending on country. Batteries have a default one year limited warranty. Refer to http://www.hp.com/support/batterywarranty/ for additional battery information. On-site service and extended coverage is also available. HP Care Pack Services are optional extended service contracts that go beyond the standard limited warranties. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: http://www.hp.com/go/cpc . ^[20]

Top Recommended Displays, Accessories and Services

P-Series

HP P27h G5 FHD Monitor	64W41AA
HP P24h G5 FHD Monitor	64W34AA

Series 3 Pro

HP Series 3 Pro 23.8 inch FHD Monitor - 324pf	9U5J5UT
---	---------

Personal Systems Hardware Support Onsite Service

HP 3 year Next Business Day Response Onsite Notebook Hardware Support	U9BA7E
---	--------

Support Services (Workforce Computing)

HP 3 year Active Care Next Business Day Response Onsite Notebook Hardware Support	U22N6E
---	--------

Wired Headset

Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X231AA
Poly Blackwire 3320 Stereo USB-C Headset +USB-C/A Adapter	8X219AA
Poly Blackwire 3210 Monaural USB-C Headset +USB-C/A Adapter	8X214AA

Speakerphones

Poly Sync 10 USB-A USB-C Speakerphone	772C3AA
---------------------------------------	---------

Backpacks

HP Everyday 16 Odyssey Gray Laptop Backpack	A08KLUT
---	---------

Wired Keyboards

HP 320K Wired Keyboard	9SR37AA
------------------------	---------

Wireless Keyboards

HP 225 Wireless Keyboard	805T1AA
--------------------------	---------

Wireless Mice

HP 235 Slim Wireless Mouse	4E407UT
----------------------------	---------

Messaging Footnotes

[1] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See <http://www.windows.com>.

[2] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[3] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 (802.11ax) are draft and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the PC to communicate with other 802.11ax devices. Wi-Fi® supporting gigabit speeds is achievable with Wi-Fi 6 (802.11ax) when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 160MHz channels.

[5] Percent of active plus non-active viewing area to active viewing area plus border. Measured with lid vertical to the desk.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. AMD's numbering is not a measurement of clock speed.

[7] Max Boost clock frequency performance varies depending on hardware, software and overall system configuration.

[12] HD content required to view HD images.

[13] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[14] Sold separately or as an optional feature.

[15] HP QuickDrop requires Internet access and Windows 10 or higher PC preinstalled with HP QuickDrop app and either an Android device (phone or tablet) running Android 7 or higher with the Android HP QuickDrop app, and /or an iOS device (phone or tablet) running iOS 12 or higher with the iOS HP QuickDrop app.

[16] 100 GB of free Dropbox storage for 12 months from date of registration. For complete details and terms of use, including cancellation policies, visit the Dropbox website at <https://www.dropbox.com/help/space/hp-promotion> . Internet service required and not included.

[17] Free 30 day subscription of McAfee LiveSafe service included. Internet access required and not included. Subscription required after expiration.

[19] Availability may vary by country.

[20] HP Care Packs are sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit <http://www.hp.com/go/cpc> . HP services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

AMD and Radeon are trademarks of Advanced Micro Devices, Inc. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

