

Hard Disk Drive / SSD / Storage Device Technical Details

Hard Disk Model	WDC WD10EURX
Disk Family	AV-GP
Form Factor	3.5"
Capacity	1 TB (1 x 1 000 000 000 000 bytes)
Disk Interface	Serial-ATA/600
Buffer-Host Max. Rate	600 MB/seconds
Buffer Size	65536 KB
Drive Ready Time (typical)	14.5 seconds
Width	101.6 mm (3.98 inch)
Depth	147 mm (5.79 inch)
Height	26.1 mm (1.02 inch)
Weight	600 grams (1.32 pounds)
Manufacturer	Western Digital Corporation

S.M.A.R.T. Values

Average temperature	Information not yet available
Average health	Information not yet available