

MobileHeat 7

including rechargeable 8.0Ah battery and charger
 EAN 4007841 085933
 Article number 085933



series 7



AMPSHare-Alliance (Bosch Professional)

1000 W

1000 W Output



150 - 550 °C



200 l/min.



9 stage temperature adjustment



Suitable for screwable nozzles



CE

Function description

With the MobileHeat 7, it is possible for the first time to carry out welding work quickly and flexibly. For this purpose, the rod device reaches up to 550 °C. But other trades, such as the electrical industry, also benefit from the simple and fast handling.

Technical specifications

Temperature	150 – 550 °C	Function, life expectancy, motor	500 h
Airflow rate	200 l/min	Function, life expectancy, heating element	300 h
Temperature setting	9-stage	Replaceable heating element	No
Settings made via	Thumbwheel	Restart protection	No
Temperature display	Thumbwheel with labelled settings	Power supply, detail	Rechargeable lithium-ion battery
Airflow control	Continuous	Thermal cut-out	Yes
Loc function	No	Dimensions (L x W x H)	385 x 115 x 89 mm
Residual heat indicator	No	PU1, net weight	1,635 kg
Motor, type	Brush motor	Manufacturer's Warranty	1 year
Heating element	Ceramic heating element	PU1, EAN	4007841085933
Rechargeable battery voltage	18 V	Scope of delivery	incl. 18V 8,0 Ah AMPSHare battery & charger
Rechargeable battery capacity	8 Ah	Output	1000 W
Interface	18V GBA Bosch rechargeable battery	Product category	Cordless hot air tool
Function, hanger	No		

Accessories

EAN 4007841 092016

Flat angled nozzle 40x2 mm

MobileHeat 7

including rechargeable 8.0Ah battery and charger
EAN 4007841 085933
Article number 085933



Accessories

EAN 4007841 092115	Flat angled nozzle 20x2 mm - angled
EAN 4007841 007812	Flat angled nozzle 20x2 mm, 100°
EAN 4007841 009083	Flat nozzle 40x2 mm perforated
EAN 4007841 092214	Round nozzle
EAN 4007841 092313	Round nozzle
EAN 4007841 009076	Round nozzle
EAN 4007841 011857	Reflector nozzle 20mm
EAN 4007841 010409	Sieve reflector nozzle 50 x 35 mm
EAN 4007841 088088	BOSCH AMPShare Battery 18V
EAN 4007841 010317	Paint Scraper Set
EAN 4007841 010423	Tarpaulin shears
EAN 4007841 035303	Heat-shrinkable tubing set for electrical installations
EAN 4007841 053963	Hot Air Tool Guard Cage HL 1820 S - HG 2320 E
EAN 4007841 084967	Pressure roller Silicone Ø 35 mm
EAN 4007841 093211	Pressure roller 50mm - Rubber
EAN 4007841 088743	BOSCH AMPShare Charger GAL 18V-40
EAN 4007841 011871	Soldering reflector nozzle
EAN 4007841 009090	Flat nozzle 60x2 mm for bitumen
EAN 4007841 011765	Fast welding nozzle 4mm narrow - for 5mm rd. noz.
EAN 4007841 011840	Fast welding nozzle 5mm narrow - for 5mm rd. noz.
EAN 4007841 010287	Fast welding nozzle 5mm - for 10mm rd. noz.