

Planer LXT®

DKP180Z

18V • 82 mm

Compact planer for heavy-duty use

A compact planer with planing depth of 2 mm and width of 82 mm. Quiet operation and easy control of cutting depth with a dial. A handy tool for trimming interior doors, panels and skirting boards. Tool only, battery and charger not included.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	15000 min ⁻¹
Planing Width	82 mm
Chip Thickness (Planing Depth)	0 - 2 mm
Max. Shiplapping Depth	9 mm
Sound Power Level (L _{WA})	95 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Planing Softwood	4,5 m/s ²
Vibration Uncertainty (K Factor), Planing Softwood	1,5 m/s ²
Tool weight with battery	3,2 - 3,5 kg
Product Dimensions (L x W x H):	333 x 157 x 160 mm

EAN 0088381662635

Link to product - www.makita.dk

User benefits

- Easy depth adjustment with the thumbwheel.
- The rubber coating on the handle ensures a firm working grip
- Electric brake for maximum productivity and increased operator safety
- Battery protection system automatically shuts off power when the battery level is low



Related products

Optional AC

122695-0 Blade Gauge Assembly 82 Mm		122793-0 Dust bag	
123062-2 Blade gauge		165581-2 Guide rule	
193540-6 Set plate		782209-3 Socket Wrench 9	
821551-8 Makpac case (3)		837808-7 MakPac (3) Inlay	
D-07945 TCT Mini Planer Blade, 82 mm		D-07967 Planer Blade T.C.T, 82 mm, 2 pcs	
D-16346 Planer blade, HSS, 82 mm, 2 pcs		D-35302 Planer blade TCT, 82 mm, 10 pcs	

Other

User manual

Parts drawing