

Planer LXT®

DKP181Z

18V • 82 mm

Powerful brushless planer with remote vacuum start capability

Hand planer for up to 3 mm planing depth and 82 mm planing width. Depth adjustment is easy with the thumbwheel. Removable chute port on left or right side. Handy for example for shortening intermediate doors or narrowing panel and moldings. Tool only, battery and charger not included.



LXT **BL** **ADT** **AWS**
MOTOR

Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	12000 min ⁻¹
Planing Width	82 mm
Chip Thickness (Planing Depth)	0 - 3 mm
Max. Shiplapping Depth	25 mm
AWS ready	✓
Sound Power Level (L _{WA})	95 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Planing Softwood	5,0 m/s ²
Vibration Uncertainty (K Factor), Planing Softwood	2,5 m/s ²
Tool weight with battery	3,3 - 3,6 kg

User benefits

- Easy depth adjustment with the thumbwheel.
- The rubber coating on the handle ensures a firm working grip
- The front of the base has 3 grooves for making chamfers.
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Chip ejection can be directed to either side of the tool
- Battery protection system automatically shuts off power when the battery level is low
- Electric brake for maximum productivity and increased operator safety

EAN 0088381890090

Link to product - www.makitauk.com



Related products

Standard AC

122785-9
Guide Rule



782209-3
Socket Wrench 9



Optional AC

122695-0
Blade Gauge Assembly 82 Mm



122785-9
Guide Rule



123004-6
Sharpening holder 82 mm



191C19-9
Blade Gauge Assembly



191C20-4
Elbow



191C22-0
Guide Assembly



191C23-8
Edge Fence



193540-6
Set plate



821551-8
Makpac case (3)



835E27-9
Makpac Type 3 Inner tray (3)



D-07945
TCT Mini Planer Blade, 82 mm



D-07967
Planer Blade T.C.T, 82 mm, 2 pcs



D-16346
Planer blade, HSS, 82 mm, 2 pcs



Other

User manual

Parts drawing