

Sander polisher LXT®

DPV300Z

18V • 50 / 75 mm • 0 - 2 800 / 9 500 min⁻¹

Compact and powerful Sander/Polisher LXT®

DPV300 Sander/Polisher LXT® is suitable for various operations, it is easy to handle and work continuously at heavy load. Variable 2-speed switch and Electronic speed control maintains constant speed under load, critical for a professional finish. Tool only, battery and charger not included.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 2 800 / 9 500 min ⁻¹
Spindle Thread	5/16 x 24UNF
Sanding Disc Diameter	50 / 80 mm
Sound Pressure Level (L _{pA})	73 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Disc Sanding	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Disc Sanding	1,5 m/s ²
Vibration Level (3 axes), Polishing	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Tool weight with battery	1,3 - 1,6 kg
Product Dimensions (L x W x H):	160 x 79 x 256 mm
Brushless Motor	✓

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Brushless maintenance-free and long-life motor
- Variable speed
- Anti-restart function minimises accidental start-up
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381735230

Link to product - www.makita.uk.com



Related products

Standard AC

140X75-2
Side Handle

191N92-5
Wool pad, 80mm

 **191N91-7**
Sponge pad 80 mm, white

 **743126-2**
Adapter



Optional AC

140X75-2
Side Handle

191N91-7
Sponge pad 80 mm, white

743124-6
Pad, 50 mm

743126-2
Adapter

E-07412
Fibre Sanding Disc, 50 mm, A60G

E-07434
Fibre Sanding Disc, 50 mm, A120G

E-07456
Fibre Sanding Disc, 50 mm, Z80G

E-07478
Surface Conditioning Disc, 50 mm

E-07490
Surface Conditioning Disc, 50 mm

E-07515
Surface Conditioning Disc, 50 mm

 **191N90-9**
Sponge pad 80 mm, yellow

 **191N92-5**
Wool pad, 80mm

 **743125-4**
Pad, 75 mm

 **781006-4**
Spanner 13 Mm

 **E-07428**
Fibre Sanding Disc, 50 mm, A80G

 **E-07440**
Fibre Sanding Disc, 50 mm, Z60G

 **E-07462**
Surface Conditioning Disc, 50 mm

 **E-07484**
Surface Conditioning Disc, 50 mm

 **E-07509**
Surface Conditioning Disc, 50 mm



Other

User manual

Parts drawing