

Belt Sander LXT®

DBS180Z

18V • 600 – 1 700 m/min • 9 mm

Narrow tool for detail work

A light and easy-to-use belt sander powered by 18V LXT® battery. The belt speed can be adjusted between 600 – 1 700 m/min. This is an ideal tool for finishing, burr removal and working in confined areas. Movable LED light. Tool only, battery and charger not included.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Belt Speed	600 - 1700 m/min
Belt Size	9 x 533 mm
Sound Power Level (L _{WA})	88 dB(A)
Sound Pressure Level (L _{pA})	80 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Sanding Metal Plate	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Sanding Metal Plate	1,5 m/s ²
Product net weight	1,4 kg
Tool weight with battery	1,8 - 2,1 kg
Product Dimensions (L x W x H):	500 x 96 x 116 mm
Angle range vertical	160 °
Vacuum cleaner connection Ø in / out	17/22 mm
Brushless Motor	✓

User benefits

- Electric brake for maximum productivity and increased operator safety
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Lock-on button for continuous operation
- Brushless maintenance-free and long-life motor
- Movable LED
- Battery protection system automatically shuts off power when the battery level is low
- Compact to storage

EAN 0088381728928

Link to product - www.makitauk.com



Related products

Standard AC

144163-3

Grip Complete 36



140W02-3

Grip Base Complete



Optional AC

122652-8

Dust nozzle Assembly



125157-7

Arm Assembly 6 mm



125158-5

Arm Assembly 9 mm



125159-3

Arm Assembly 13mm



140W02-3

Grip Base Complete



144163-3

Grip Complete 36



198043-5

Grip 36 set



P-43181

Sanding belt 6 x 533 mm, 40G, 5 pcs



P-43197

Sanding belt 60G



P-43206

Sanding belt 6 x 533 mm, 80G, 5 pcs



P-43212

Sanding belt 6 x 533 mm, 100G, 5



P-43228

Sanding belt 6 x 533 mm, 120G , 5



P-43256

Sanding belt 9 x 533 mm, 40G, 5 pcs



P-43262

Sanding belt 9 x 533 mm, 60G, 5 pcs



P-43278

Sanding belt 9 x 533 mm, 80G, 5 pcs



P-43284

Sanding belt 9 x 533 mm, 100G, 5



P-43290

Sanding belt 9 x 533 mm, 120G, 5



P-43321

Sanding belt 13 x 533 mm 40G, 5 pcs



P-43337

Sanding belt 13 x 533 mm, 60G, 5



P-43343

Sanding belt 13 x 533 mm, 80G, 5



P-43359

Sanding belt 13 x 533 mm, 100G, 5



P-43365

Sanding belt 13 x 533 mm, 120G, 5



Other

User manual

Parts drawing