

18V Trimmer Brushless LXT®, DRT52Z

1/4"



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	30000 min ⁻¹
Plunge capacity	0 - 42 mm
Collet Capacity	6 mm
Sound Power Level (L _{WA})	89 dB(A)
Sound Pressure Level (L _{pA})	81 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Rotation Without Load	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Rotation Without Load	1,5 m/s ²
Product net weight	0,95 kg
Tool weight with battery	1,3 - 1,6 kg
Product Dimensions (L x W x H):	134 x 90 x 220 mm

User benefits

- Brushless maintenance-free and long-life motor
- Soft start for smooth start-ups
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

EAN 0197050005106

Link to product - www.makitauk.com



Related products

■ Standard AC

122703-7

Trimmer Guide Assembly



122704-5

Straight Guide



191Y82-4

Straight Bit Set, 6 Mm



193936-1

ACCESSORY SET

418647-0

Chip Deflector



■ Other

User manual

Parts drawing