

2YEAR WARRANTY
BRITISH BRAND

MITCHELL & BROWN
JB-40DU1811

40" | FULL HD | SMART TV POWERED BY TIVO



General

Model Number	JB-40DU1811
EAN	5055862344187
Energy Rating	G
Tuner Broadcasting	DVB-T/T2
Colour	Black
Hotel Mode	Yes
Operating System	TiVo

Display

Screen Size	40"
Resolution Size	1920 x 1080
Resolution Type	Full HD
Screen Type	LCD

Video

Screen Mirroring	Yes
HDR Game Mode	Yes
HDR Type	HDR 10, HLG

Audio

Sound Enhancement	DAP
Supports High-Resolution	No
Noise Reduction	Yes
Headphone Socket	Yes
Audio Power	2x8W

Connectivity

HDMI Input	2
HDMI ARC (Audio Return Channel)	Yes
USB Input	1
Scart Input	No
WiFi	Yes
Ethernet	Yes

Smart Features

Freely	Yes
Bluetooth	Yes
Smart Apps	Netflix, Prime Video, Disney +, Youtube

Power and Energy

Energy Efficiency Class	G
Energy Saving Mode	Yes
Annual Power Consumption (kWh)	37
On-mode Power Consumption (W)	37
Standby Power Consumption (W)	0.5

Dimensions

Set Size without Stand (WxDxH)	902 x 87 x 517
Set Size with Stand (WxDxH)	902 x 87 x 553
Package Size (WxDxH)	985 x 145 x 608
Product Weight (KG)	6
Unit Packaged Weight (KG)	8.25
VESA Wall Mount Size	100x100