

2YEAR WARRANTY
BRITISH BRAND

MITCHELL & BROWN
JB-43DU1811

43" | 4K ULTRA HD | SMART TV POWERED BY TIVO



General

Model Number	JB-43DU1811
EAN	5055862344194
Energy Rating	G
Tuner Broadcasting	DVB-T/T2
Colour	Black
Hotel Mode	Yes
Operating System	TiVo

Display

Screen Size	43"
Resolution Size	3840 x 2160
Resolution Type	Full HD
Screen Type	LCD

Video

Screen Mirroring	Yes
HDR Game Mode	Yes
HDR Type	Dolby Vision, HDR 10, HLG

Audio

Sound Enhancement	Dolby Atmos
Supports High-Resolution	Yes
Noise Reduction	Yes
Headphone Socket	Yes
Audio Power	2x8W

Connectivity

HDMI Input	3
HDMI ARC (Audio Return Channel)	Yes
USB Input	2
Scart Input	No
WiFi	Yes
Ethernet	Yes

Smart Features

Freely	Yes
Bluetooth	Yes
Smart Apps	Netflix, Prime Video, Disney +, Youtube

Power and Energy

Energy Efficiency Class	G
Energy Saving Mode	Yes
Annual Power Consumption (kWh)	72
On-mode Power Consumption (W)	72
Standby Power Consumption (W)	0.5

Dimensions

Set Size without Stand (WxDxH)	965 x 87 x 561
Set Size with Stand (WxDxH)	965 x 266 x 598
Package Size (WxDxH)	1055 x 145 x 660
Product Weight (KG)	7
Unit Packaged Weight (KG)	9.25
VESA Wall Mount Size	100x100