

KAUDEN™

Item code – SM606V/C6/WH
CAT6 RJ45 White Data Module 25x50mm



- Fits 25x50mm aperture , just snap it in
- Performs to UK/EU standard BS EN 50173-6
- Clear hinged label cover for ease of use
- Standard IDC terminals including cable tie
- Flame retardant to UL94-V2 and colour coded for 568B wiring (most common used)

Supplied in dark grey colour to match the popular fashion for grey electrical accessories in the home and office. Mainly used in decorative face plates together with Data Module .

CAT6 is the standard set to support data transmissions at frequencies up to 250 Mhz over 100 ohm twisted pair cable . Commonly used to support many Data applications. More than double the information carrying capacity of Cat5e . 25x50mm size modules are sometimes referred to as “ Euro Modules” and can be used in any of the KAUDEN plastic or decorative faceplate ranges

General

Sale Unit one piece plus cable tie in polybag with barcode
Barcode 5028088011430
Weight Packed 0.015 Kg
Dimension Packed 110x70x20 mm
Height Width Depth
Commodity Code 85177000

For Trade and Bulk buyers

Carton Quantity 10
Dimension 4x12x15 cm
Weight 0.196 kg

Technical

Specification CAT6 performance tested to EN 50713
Terminals Krone Type IDC
Socket RJ45 Unshielded
Colour White

