

13ft (4m) Premium Certified HDMI 2.0 Cable - High-Speed Ultra HD 4K 60Hz HDMI Cable with Ethernet - HDR10, ARC - TPE Jacket - UHD HDMI Video Cord - For UHD Monitors, TVs, Displays - M/M

Product ID: HDMMV4M



This Premium High Speed HDMI 2.0 Certified Cable supports resolutions of up to 4K at 60Hz (3840x2160p), 18Gbps bandwidth, High Dynamic Range (HDR10), and Dolby Vision for a higher contrast ratio and vivid colors.

The cable also features Audio Return Channel (ARC) with up to 32 uncompressed 5.1 and 7.1 digital audio channels to support DTS-HD Master Audio, DTS:X, Dolby TrueHD, and Dolby Atmos for high-quality sound.

The cable has undergone rigorous compliance testing and is certified by an HDMI Authorized Test Center to ensure it supports high-bandwidth enabled features. An EMI test is performed to ensure minimal interference from wireless signals.

- Aluminum-mylar foil with braided shielding improves EMI protection
- Long-lasting flexible TPE jacket and strain reliefs
- TPE is a non-toxic and halogen-free
- Corrosion-resistant gold-plated connectors ensure premium video quality and enhanced reliability

This premium cable has been tested to withstand 10,000+ insertions.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

Features

- **HIGH PERFORMANCE CABLE:** 13ft (4m) Premium Certified High-Speed HDMI cable with Ethernet supports 4K 60Hz (3840x2160), 18Gbps bandwidth, HDR10, Ultra-wide aspect ratio, ARC, 3D video, 32 Ch audio (5.1/7.1/Dolby TrueHD/Atmos), BT.2020 colorimetry
- **PREMIUM HDMI 2.0 CABLE:** Ultra HD 4K 60Hz HDMI cord is engineered and built to improve signal integrity - Featuring connector bodies encased in die-cast aluminum to prevent EMI induced signal degradation; Corrosion-resistant gold-plated connectors
- **DURABLE:** Tested to withstand 10,000+ insertions & 600+ bend cycles at 120 angle; TPE outer jacket with molded strain relief absorbs stress from frequent bends; TPE is flexible, environmentally friendly, non-toxic, halogen-free, and RoHS compliant
- **APPLICATIONS:** Ideal for home/office, works with computer/laptop/desktop/PC/workstation - UHD HDMI cord to connect TV/monitor/display/projector, Samsung/Sony/Apple TV/Dell/LG - Works w/ HDMI 2.0 Ultra HD, and other resolutions
- **SPECS:** 13 feet (4 meter) - HDMI 2.0 - Premium Certified HDMI Cable - High-Speed Cable with Ethernet - Color: Gray and Black - HDMI Male to Male - Outer Diameter: 0.25" (6.5 mm) - 28 AWG - Jacket: TPE - EMI Shield: Al-Mylar Foil Braid

Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Video Revision	HDMI 2.0b
Maximum Data Transfer Rate	18Gbps

Maximum Cable Length	13.1 ft [4 m]
Maximum Digital Resolutions	4K 60Hz 3840x2160
Audio Specifications	HDMI - 32 Channel Audio
	HDMI - 7.1 Channel Audio
	HDMI - 5.1 Channel Audio

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Environmental

Operating Temperature	0 to 50C (32 to 122F)
Storage Temperature	0 to 50C (32 to 122F)
Humidity	0%RH ~ 85%RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	13.1 ft [4 m]
Cable OD	0.3 in [6.5 mm]
Product Length	13.1 ft [4.0 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.1 cm]
Weight of Product	8.1 oz [229.0 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [32.9 cm]

Package Width	5.3 in [13.5 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	8.7 oz [246.0 g]

What's in the Box

Included in Package	1 - Premium High Speed HDMI Cable
---------------------	-----------------------------------

****Product appearance and specifications are subject to change without notice.***