

66ft (20m) Active HDMI Cable - 4K High Speed HDMI Cable with Ethernet - CL2 Rated for In-Wall Install - 4K 30Hz Video - HDMI 1.4 Cord - For HDMI Monitor, Projector, TV, Display

Product ID: HDMM20MA



This High Speed HDMI Cable with Ethernet is designed to deliver superior video and audio performance while ensuring reliable connectivity with a variety of HDMI devices, including HDTVs, stereo receivers, projectors, gaming consoles, and more. The active cable also features a thinner wire construction for more flexibility, making it ideal for in-wall installations.

High Speed HDMI

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), Full HD (1920x1080p at up to 120Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

Premium Build Quality

Constructed with 24 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. The cable's built-in amplifier circuitry actively boosts the HDMI signal with no external power required. It supports longer connections than regular HDMI.

Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please ensure that the HDMI connector labelled with "TV" is connected to the display, in order to ensure that the device and the HDMI source are connected properly.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

- Connect your high-definition A/V devices such as streaming media players (Roku, Apple TV), game consoles (Xbox One, PS4), Blu-ray Disc or DVD players over long distances, with no signal loss

Features

- **HIGH SPEED HDMI CABLE:** 65.6 ft (20m) Active HDMI Cable with Ethernet supports 4K Ultra HD video (3840x2160p, 24, 30Hz 4096x2160p, 24Hz), Full HD (1080p 120Hz) HDMI 1.4b wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **ACTIVE CIRCUITRY:** Active bus powered amplifier boosts video signals over longer distances to extend HDMI signal up to 65.6 ft (20m) (no external power supply needed), supports additional color spaces such as Adobe RGB and YCC601 Color
- **DURABLE CABLE:** Ideal for in-wall installations where CL2 rating is required; Flexible PVC jacket; Al-Mylar Foil with Braid shield & gold plated connectors with metal shell improve signal integrity & block external Electromagnetic Interference (EMI)
- **APPLICATIONS:** Use this long HDMI cable for home office, conference room, office or classroom; works w/ your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projectors/large HDTV displays; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 65.6 feet (20 meters); Black; HDMI 1.4b; HDMI Cord Male to Male; Jacket: PVC; Shield: Al-Mylar foil w/ Braid; CL2 Fire Rated; ARC, Deep Color, HDCP 1.4, CEC; Note: Cable is unidirectional with Source and Display labels

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | 2 Years |
| Connector Plating | Gold |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |
| Fire Rating | CL2 |
| Chipset ID | Redmere - RM1691 |

Performance

| | |
|-----------------------------|-----------------|
| Maximum Digital Resolutions | 4K x 2K @ 30 Hz |
|-----------------------------|-----------------|

| | | |
|-------------------------------------|---------------------------|---|
| Connector(s) | | |
| | Connector A | 1 - HDMI (19 pin) |
| | Connector B | 1 - HDMI (19 pin) |
| Special Notes / Requirements | | |
| | Note | This HDMI Cable is unidirectional with identified connectors for Source and Display. Please ensure that the HDMI connector labelled with "Display" is connected to the Display, TV, or Projector. |
| Physical Characteristics | | |
| | Color | Black |
| | Connector Style | Straight |
| | Wire Gauge | 24 AWG |
| | Cable Length | 65.6 ft [20 m] |
| | Cable OD | 0.3 in [8.5 mm] |
| | Product Length | 65.6 ft [20.0 m] |
| | Product Width | 0.8 in [2.0 cm] |
| | Product Height | 0.4 in [9.0 mm] |
| | Weight of Product | 3.4 lb [1.5 kg] |
| Packaging Information | | |
| | Package Quantity | 1 |
| | Package Length | 10.5 in [26.7 cm] |
| | Package Width | 10.6 in [26.8 cm] |
| | Package Height | 3.0 in [7.7 cm] |
| | Shipping (Package) Weight | 3.8 lb [1.7 kg] |
| What's in the Box | | |
| | Included in Package | 1 - 20m Active CL2 In-Wall High Speed HDMI Cable - HDMI - M/M |

**Warranty
Information**

Warranty

2 Years

****Product appearance and specifications are subject to change without notice.***