



NYS229

1/4" open jack, mono 2 pole, with washer and nut, with 0.205" faston tabs

Article Variations

Article Name	Details	Packaging
NYS229	for up to 3.5 mm panel thickness	
NYS229L	for up to 6.5 mm panel thickness	

Technical Information

Product	
Title	NYS229
Connection Type	Jack

Electrical

Contact resistance	$\leq 10\text{m}\Omega$
Insulation resistance	$\geq 2000\text{M}\Omega$
Dielectric strength	50Hz 500VAC

Mechanical

Insertion and Withdrawal force	4.5-40N
Lifetime	>5000 mating cycles

Material

Contact	QSn6.5-0.1 δ 0.5 T
Contact	H62 δ 0.5 Y2
Base	Brass
Gasket	Steel
Nut	Brass
Contact	Tin and Ce
Contact	Tin and Ce