



21.5" and 32" Full HD, LED Input Monitor - HDMI, VGA and BNC (32" only)

VM215e & VM32



Above: VM215e connectors



Above: VM32 connectors (USB for future development of firmware)

The VM215e (21.5") and VM32 (32") monitors produce high resolution, high contrast images via standard HDMI and VGA inputs.

In addition, the VM32 provides a BNC In and Out passive loop through allowing the monitor to be used for CVBS images with no loss in image quality. This makes it ideal for use as an entrance monitor displaying a local CVBS camera image which is then transmitted back to a DVR for recording.

Both monitors benefit from an Energy Saving Mode reducing running costs and environmental impact - lowering consumption to less than, or equal to, 0.5Watt.

A fast response 6.5mS and 8mS (respectively) reduces motion blur.

An intuitive multilingual menu system inc. English, French, German, Spanish and Italian, makes the monitors simple to set-up.

The monitors are supplied with a desktop plinth and VESA mounting capabilities via VESA 75x75 and 200x100, respectively. Therefore, the monitors can be mounted anywhere in combination with our VESA mounting bracket offerings.

To learn more about Vista's NDAA compliant video surveillance products please visit www.norbain.com/brands/vista

KEY FEATURES

Low energy consumption,
long service life panel

High contrast ratio
and luminance

Rapid response time, no
trailing image

TEL
+44 (0) 118 912 5000



* To scan the QR code, make sure your phone/device has a suitable reader. Most modern Android and iOS smartphone cameras will automatically scan the code and provide the product's URL link, which will open from the device's web browser.

TECHNICAL SPECIFICATION

Model	VM215e	VM32
Panel type	LCD with LED backlight	
Screen size - Diagonal	21.5"	32"
Aspect Ratio	16:9	
Viewable size (H × V)	478.656mm × 260.28mm	698.40mm × 392.85mm
Dot pitch (H × V)	0.241mm × 0.241mm	0.36mm × 0.36mm
Viewing angle (L/R/T/B)	178° / 178°	
Contrast ratio	3000:1	1200:1
Brightness	250 cd/m2	300 cd/m2
Resolution	1920 × 1080	
Response time	6.5ms	8ms
HDMI input	1	
VGA Input	1	
BNC In output	n/a n/a	1 1 (CVBS)
Audio Input	1 (3.5mm jack)	
Speaker built-in	1watt × 2	5watt × 2
OSD languages	CH / DE / EN / FR / IT / SP	
Power input	12vDC 2.0A	AC 100 - 240V
Power consumption	<22W	<65W
Power saving	≤0.5W	
Operating temperature/ humidity	0°C - 40°C/10% - 85%	
Storage Temperatures	-20°C - 60°C	
Accessories	HDMI and VGA cable, Power cable, Adapter (VM215 only), pedestal	
Dimension net W × H × D	492.7mm × 280.9mm × 50.8mm	735.8mm × 433.46mm × 80.19mm
Dimension gross W × H × D	560mm × 398mm × 114mm	810mm × 545mm × 165mm
Weight net/gross	2.9Kg/3.8Kg	9.8Kg / 11.8Kg
Wall mount VESA	75 × 75	200 × 100
Regulation	CE/UKCA	
Warranty	2 Years	
Advance replacement	2 Years	

MODELS IN THIS RANGE

0950090 VM215e
21.5" Monitor with HDMI & VGA

0922950 VM32
32" Monitor with HDMI, VGA and BNC

ASSOCIATED PRODUCTS

0911910 LCD-IMPGA-b
TFT Pole Girder Adapter Black



0911920 LCD-IPMCA-b
TFT Pole Ceiling Adapter



0958070 VB-38P2M2HC
38mm diameter Pole 2m Chrome

0898200 VCBDEL2MB
38mm X 2m Black Pole

0911700 VDM-C
Black Internal Coupler for VCBDEL2MB

VM215e ACCESSORIES

0911930 VESAPA1-b
Single TFT Pole Adapter



0857990 VESAPMX
Monitor Pole Clamp 30-55mm diameter



0498620 VESAWM
Vesa 75/100 Wall Bracket



0498630 VESAWMPT
Vesa 75/100 Tilt/turn Wall Bracket



VM32 ACCESSORIES

0911940 VK2PVMPA1-b
Single Vesa200x100 Swivel mount



0911950 VK2PVMPA1-b
Double Vesa200x100 Swivel mount



OTHER PRODUCTS

0925550 VistaPC-i5-G13-4Mon-KBM ClientPC
Windows Client i5 PC with 0TB onboard storage, 4-monitor support

0925560 VistaPC-i5-G13-4Mon-KBM-2TB Srv/Client
Windows Client i5 PC with 2TB onboard storage for exported evidence storage, 4-monitor support

0946300 Diamond4Kv2
All in one CCTV\IP\Cable Test Monitor