

CHERRY XTRFY M42 RGB

Ultra-light gaming mouse



Models may vary from the image shown

HIGHLIGHTS

- Adjustable symmetrical shape
- Ultra-light construction
- Pixart 3389 sensor
- Modular shell – two sizes (included)
- 1.8 m CHERRY XTRFY EZcord*

VERSATILE SHAPE. SOLID PERFORMANCE.

Ultra-light construction. State-of-the-art components. And a symmetrical shape with interchangeable parts that let you adjust its size. The M42 is designed to be the perfect fit for any gamer.

5 EDITIONS.

Black, White, Retro, Miami Blue and Pink. The M42 is a part of CHERRY XTRFY's Project 4 and comes in 5 different editions, allowing you to match it with mousepads, mouse bungees and keyboards in the same colorways. Pick a color and build your perfect setup.

ADJUSTABLE SYMMETRICAL SHAPE.

Palm, claw or fingertip grip? With its ambidextrous shape and interchangeable parts, the M42 is designed for a comfortable fit – no matter the size of your hand or the style of your grip.

STATE-OF-THE-ART COMPONENTS

Pixart's highest-performing gaming sensor, 3389. Pro player-optimized Omron switches, rated for 20 000 000 clicks. The M42 is equipped with nothing but top-grade components.

EFFORTLESS SWIPES.

The M42 features 100 % PTFE skates with rounded edges for smoother glide, while its matte UV coating in combination with the hole structure make for a steadier grip. Enhancing airflow under your palm, the holes also help you stay comfortable.

ULTRA-LIGHT YET DURABLE.

The M42 is built on the principle that lower weight must never mean lower quality. It doesn't matter how light your mouse is if it can't withstand heavy daily use. With a construction that's engineered to minimize weight while retaining durability, the M42 is made to last.

RGB ILLUMINATION.

With customizable lighting, it's easy to add your personal touch to the M42. Choose your color. Switch between numerous LED effects. Adjust the brightness. Or turn the illumination off. All settings are made directly on the mouse.

ULTRA-LIGHT IS EVEN LIGHTER WITH THE CHERRY XTRFY EZCORD®.

To make smooth swipes even smoother, we created the CHERRY XTRFY EZcord. Softer, lighter and more flexible. With a color to match your choice of mouse.

ARM 32-BIT MICROCONTROLLER.

Fast swipes require high-speed processing. The M42 is powered by an ARM 32-bit microcontroller for uncompromising speed and stability.

DUST AND SPLASH RESISTANT.

We've covered the inside of the mouse in conformal coating to protect the components against dust, splashes and LAN night mishaps.

PRODUCT SPECIFICATIONS

Scope of delivery:	• Mouse • Modular shell • 2 x Keycaps • Spare mouse feet • Manual
--------------------	---

Illumination: RGB

TECHNICAL DETAILS

Cable length:	180 cm
Thumb buttons:	yes
CPI settings:	400 - 16000
Polling rate:	• 125 Hz • 500 Hz • 1000 Hz
IPS:	400
Max. acceleration:	50g
Surface:	UV-coated

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

SKU / EAN / UPC	Protection class	Colour	Illumination
M42-RGB-BLACK EAN 7340086909440 UPC 842597101315	Standard	black	RGB
M42-RGB-BLUE EAN 7340086909471 UPC 842597101346	Standard	blue	RGB
M42-RGB-PINK EAN 7340086909488 UPC 842597101353	Standard	pink	RGB
M42-RGB-RETRO EAN 7340086909464 UPC 842597101339	Standard	grey	RGB
M42-RGB-WHITE EAN 7340086909457 UPC 842597101322	Standard	white	RGB

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.