PRO-LITE

Product Data Specification

PRO-LITE - FLDD BUTTERFLY LAMP

DESCRIPTION

- · Low energy, long life
- Double D Butterfly Lamp
- 16W, 28W, 38W
- 2 pin and 4 pin versions

APPLICATIONS

- Domestic & Commercial
- Bulkheads Indoor & Outdoor

FEATURES

- 10,000 Hr average lamp life
- 2 & 4 Pin configuration
- High light output low energy
- Compatible with all current control gear
- Available Col 3500K, 2700K on request



TECHNICAL SPECIFICATION



				Colour			Average	Dim.	Dim
	Power			Temp.	Сар	Lumens	Life	(mm)	(mm)
Order code	W	No. Pins	Colour	K	Type	lm	h	L	W
FLDD/1635/PRO	16	2	WHITE	3500K	GR8	1050	10000	132	132
FLDD/2835/PRO	28	2	WHITE	3500K	GR8	2250	10000	196	196
FLDD/3835/PRO	38	2	WHITE	3500K	GR8	3000	10000	198	198
FLDD4/1635/PRO	16	4	WHITE	3500K	GR10q	1050	10000	132	132
FLDD4/2835/PRO	28	4	WHITE	3500K	GR10q	2250	10000	196	196
FLDD4/3835/PRO	38	4	WHITE	3500K	GR10q	3000	10000	198	198