



Einhell

CLASSIC

Hot Air Gun

TC-HA 2000/1

Item No.: 4520184

Ident No.: 21034

Bar Code: 4006825602227

The TC-HA 2000/1 hot air gun is a powerful tool which provides good service to DIY enthusiasts on jobs involving the removal of old lacquer and paint, the fitting of plastic tubes, and much more besides. There are two power settings to adjust the temperature and air rate to the particular requirements.

Features & Benefits

- High-power hot air gun, 2 power settings
- 2 temperature and air flow settings
- Stable base, suitable for stationary applications as well
- Overheating protection for safe operation
- Great versatility by included accessories

Technical Data

- Mains supply	230/240 V 50 Hz
- Power	2000 W
- Temperature at setting 1	350 °C
- Temperature at setting 2	550 °C
- Airflow rate at setting 1	300 L/min
- Airflow rate at setting 2	500 L/min

Logistic Data

- Product weight	0.68
- Gross weight single packaging	1 kg
- Dimensions single packaging	240 x 81 x 240 mm
- Pieces per export carton	10 Pieces
- Gross weight export carton	11.3 kg
- Dimensions export carton	480 x 425 x 225 mm
- Container quantity (20"/40"/40"HC)	5200 10800 13000



2 TEMPERATURE SETTINGS



STATIONARY USE POSSIBLE

