



Nylon Black & Natural Cable Ties

Product Type:

Nylon Black & Natural Cable Ties

Product Details:

Material Natural: Polyamide (Nylon) 6.6 natural

Material Black: Polyamide 6.6 natural+ ~1% carbon black

Flammability of raw material: UL 94 - V2, Plenum Rated AH-2(Low Smoke)

Humidity absorption: 2,7% - 2,8% (23°C -50%RH)

Working (Operation) Temperature: -40°C - + 85°C (-40°F - + 185°F)

Min Installation Temperature: -20°C (-4°F)

Max sustainable temperature for short time: +110°C (230°F)

EN (IEC) 62275:2019, RoHS, REACH Compliance, Halogen Free

Application:

Natural and Black coloured Nylon cable ties suitable for bundling cable. Manufactured in Nylon 6/6 and resistant to petrol, oils, greases and alkalis. Available in a range of popular sizes with some sizes available to buy in bulk packs.

Part No.	Replace * for Col.	Black	Natural	Size	Max Bundle Diameter	Tensile Strength	Pack Qty
ACT75X2.4 *	B		N	2.5X80	14.0mm	80N(18lb)	100
ACT100X2.5 *	B		N	2.5X100	20.5mm	80N(18lb)	100
ACT120X2.5 *	B		N	2.5X120	27.0mm	80N(18lb)	100
ACT150X2.5 *	B		N	2.5X150	36.5mm	80N(18lb)	100
ACT165X2.5 *	B		N	2.5X160	39.8mm	80N(18lb)	100
ACT203X2.5 *	B		N	2.5X200	52.5mm	80N(18lb)	100
ACT150X3.6 *	B		N	3.6X150	36.0mm	180N(40lb)	100
ACT203X3.6 *	B		N	3.6X200	52.5mm	180N(40lb)	100
ACT292X3.6 *	B		N	3.6X300	84.0mm	180N(40lb)	100
ACT160X4.8 *	B		N	4.6X160	36.6mm	230N(50lb)	100
ACT190X4.8 *	B		N	4.6X190	46.0mm	230N(50lb)	100
ACT200X4.8 *	B		N	4.8X200	49.5mm	230N(50lb)	100
ACT250X4.8 *	B		N	4.8X250	65.0mm	230N(50lb)	100
ACT300X4.8 *	B		N	4.8X300	81.0mm	230N(50lb)	100
ACT368X4.8 *	B		N	4.8X370	103.5mm	230N(50lb)	100
ACT450X4.8 *	B		N	4.8X450	129.0mm	230N(50lb)	100
ACT203X7.6 *	B		N	7.6X200	50.9mm	540N(120lb)	100
ACT300X7.6 *	B		N	7.6X300	82.8mm	540N(120lb)	100
ACT380X7.6 *	B		N	7.6X380	108.0mm	540N(120lb)	100
ACT550X8.0 *	B		N	8.0X550	163.5mm	800N(175lb)	50
ACT760X8.8 *	B		N	8.8X760	229.5mm	800N(175lb)	50
ACT610X9.0 *	B		N	9.0X610	181.5mm	800N(175lb)	50
ACT710X9.0 *	B		N	9.0X710	195.0mm	800N(175lb)	50
ACT812X9.0 *	B		N	9.0X810	245.0mm	800N(175lb)	50
ACT914X9.0 *	B		N	9.0X920	280.0mm	800N(175lb)	50
ACT1219X9.0 *	B		N	9.0X1220	375.5mm	800N(175lb)	50
ACT280X12.7 *	B		N	12.7X290	76.0mm	1200N(250lb)	25
ACT380X12.7 *	B		N	12.7X380	103.5mm	1200N(250lb)	25
ACT480X12.7 *	B		N	12.7X480	136.0mm	1200N(250lb)	25
ACT580X12.7 *	B		N	12.7X580	168.0mm	1200N(250lb)	25
ACT730X12.7 *	B		N	12.7X730	216.0mm	1200N(250lb)	25
ACT880X12.7 *	B		N	12.7X880	263.0mm	1200N(250lb)	25
ACT1030X12.7 *	B		N	12.7X1030	315.0mm	1200N(250lb)	25

BULK PACKS

ACT100X2.5 * BP	B	N	Cable tie 2.5-100 Bulk Pack	500
ACT150X3.6 * BP	B	N	Cable tie 3.6-150 Bulk Pack	500
ACT203X3.6 * BP	B	N	Cable tie 3.6-203 Bulk Pack	500
ACT160X4.8 * BP	B	N	Cable tie 4.8-160 Bulk Pack	500
ACT250X4.8 * BP	B	N	Cable tie 4.8-250 Bulk Pack	500
ACT300X4.8 * BP	B	N	Cable tie 4.8-300 Bulk Pack	500
ACT368X4.8 * BP	B	N	Cable tie 4.8-368 Bulk Pack	500
ACT380X7.6 * BP	B	N	Cable tie 7.6-380 Bulk Pack	500