








Color: ■ dark gray/yellow





Physical data		
Width		38.3 mm / 1.508 inches
Height		23.7 mm / 0.933 inches
Depth from upper-edge of DIN-rail		35.4 mm / 1.394 inches
Depth		40.3 mm / 1.587 inches

Mechanical data		
Mounting type		Snapping on DIN-15 rail
Suitable		for 10-wire connectors (4 mm²)

Material data		
Note (material data)		Information on material specifications can be found here
Color		dark gray/yellow
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.193 MJ
Weight		6.4 g

Commercial data		
PU (SPU)		10 pcs
Packaging type		Box
Country of origin		CN
GTIN		4066966603903
Customs tariff number		39269097900

Product classification		
UNSPSC		39121409
ETIM 9.0		EC002848
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 221-539/002-053	



1 Compatible Products
1.1 Optional Accessories
1.1.1 Marking
1.1.1.1 Marking strip



Item No.: 210-833
Marking strips; 25 m on roll; 6 mm wide;
plain; Self-adhesive; white