



DCS380N-XJ 18V Reciprocating Saw – Bare Unit



- Pivoting adjustable shoe with open top for high stability and blade visibility during a cut
- Intelligent variable speed trigger, lock-off switch and electronic motor brake for quick controlled cuts and enhanced work safety
- Lever-action keyless blade clamp for quick and easy blade changes
- Powerful & Highly Efficient PM58 DEWALT fan cooled motor with replaceable brushes, delivers fast cutting action up to 2,950 strokes per minute and 28.6 mm stroke length maximising user productivity
- Part of the intelligent XR Lithium-Ion Series designed for efficiency and making applications faster

Specifications:

- Power Source – Cordless
- Battery Technology – Lithium ion
- Voltage – 18V
- Power – 560W
- Weight – 2.7 Kg
- Stroke Length – 28.6mm
- No Load Stroke Rate – 0-2950spm
- Sound Pressure – 88 dB (A)
- Sound Power – 99 dB (A)
- Sound Uncertainty – 3 dB (A)
- Vibration emission cutting board – 31 m/s²
- Vibration Uncertainty cutting board – 8.1m/s²
- Vibration emission wooden beam – 33 m/s²
- Vibration Uncertainty wooden beam – 6.6m/s²

Supplied with:

- DCS380 18V Reciprocating Saw

1 YEAR LIMITED WARRANTY, 3 YEAR LIMITED WARRANTY WHEN REGISTERED We're confident of the quality of our products and we'll repair, without charge, any defects due to faulty materials or workmanship within the specified warranty. For more information please visit <https://www.dewalt.co.uk/support/support-information>