


EVSG-ORD 16 BK

Stop end with mounted O-Ring, polyamide, RAL 9005, M16



Products may differ in size, colour and appearance to those shown. If you require further information or customisation, please contact us directly.



Material	Polyamide, fibre reinforced
Material sealing gasket	EPDM
Temp. range min	-40 °C
Temp. range max	100 °C
Glow wire test	650 °C
Protection class	IP66 / IP68 (5 bar 30 min)
Thread type	M
Ø Connection thread D	16
Lead	1,5
Length screw-in thread L	6 mm
Total length TL	9 mm
External diameter ED	20 mm
Product Color	RAL 9005
Order no. RAL 9005	10064643
Type	EVSG-ORD 16 BK
Packing unit	100
EAN number	4007685646437
Tariff number	39269097
ETIM-Classification	EC000032

Recommended accessories

EMUG 16 BK	10061781
-------------------	-----------------

02.09.2025


Your Contact:

WISKA Hoppmann GmbH

Kisdorfer Weg 28 · 24568 Kaltenkirchen · Germany

☎ +49-4191-508-0 · 📠 +49-4191-508-209

contact@wiska.de · www.wiska.com



Your Contact:

WISKA Hoppmann GmbH

Kisdorfer Weg 28 · 24568 Kaltenkirchen · Germany

☎ +49-4191-508-0 · 📠 +49-4191-508-209

contact@wiska.de · www.wiska.com

Other technical data on request / subject to change without notice