

SHARK 6802 AW

SHARK SIXEIGHT



Products may differ in size, colour and appearance to those shown. If you require further information or customisation, please contact us directly.

Material	Polyamide
Filling	Silicone
Temp. range min	-20 °C
Temp. range max	90 °C
Glow wire test	self-extinguishing
Protection class	IP68
Voltage	0,6 kV - 1 kV
Type	SHARK 6802 AW
UK-Number	SH6802AW
WISKA-Order no.	10108954
Packing unit	1
ETIM-Classification	EC001169

Remarks:

Ampere: 80

Cable Size: (5 core) 2.5 - 10 mm

LxBxH: 235x68x48 mm

Description:

SHARK SIXEIGHT IP 68 rated pre-filled gel insulated joint, including modular bolts and gaskets, cable retention clamp, spring coil and earthing braid.

Additional Info:

Ready to use, re-enterable, 100% watertight, 100% dust-tight, suitable for SWA cables, no mixing or pouring, immediate operation, excellent electrical insulation, good mechanical strength, no expiry date.

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

 +44-12-08816062 ·  +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk

03.09.2025

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

☎ +44-12-08816062 · ☎ +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk