



Sensing Distance: 6m -10m
Time: 1 minute
LUX: 10 Lux - 45 Lux

Rectangular Solar Bollard LED

Features

Specification



IP54



- Modern die-cast solar powered aluminium LED bollard suitable for domestic applications.
- Graphite textured powder coat paint finish provides enhanced durability.
- PIR motion sensor modes:
- **Mode 1:** 15% output after sunset, motion detected 100% output, no motion 15% for 20 hours..
- **Mode 2:** Motion detected 100% output, no motion off.
- LED lifespan L70 36,000 hours.

SKU Code	Description	Lumens Delivered	CCT
4L2/6005	Solar Bollard LED	230	4000K

