

1U Adjustable Vented Server Rack Mount Shelf - 175lbs - 19.5 to 38in Adjustable Mounting Depth
Universal Tray for 19" AV/ Network Equipment Rack - 27.5in Deep - TAA

Product ID: ADJSHELF



The ADJSHELF Adjustable Mounting Depth Rack Mount Shelf offers a simple way to effectively organize mission critical computer hardware in your server racks and cabinets.

Compatible with all 19in (wide) server racks/cabinets, the fixed rack shelf can be adjusted from 19in to 38in (mount depth) as necessary. A sturdy cold-rolled steel construction provides long term durability and enables a weight capacity of up to 175 lbs (80 kg).

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility



Applications

- For use with all 19" wide Server Racks and Cabinets
- Supply additional storage space for mission critical hardware.

Features

- **UNIVERSAL 19" FIT:** This vented server rack mount shelf is designed to fit any 19in server rack and has a fixed surface depth of 27.56in (70cm), and an adjustable mounting depth range of 19.5-38in (50-97cm) for your data,

networking or other equipment

- **MAXIMIZE VENTILATION:** The vented shelf ensures consistent airflow to effectively dissipate heat on servers; It also works great to keep your computer and AV equipment cool
- **HEAVY-DUTY & DURABLE DESIGN:** Constructed with SPCC commercial cold-rolled steel, the sturdy IT-grade cabinet shelf ensures long term durability and supports a total weight load of 175lb (80kg)
- **VERSATILE FUNCTIONALITY:** With a surface depth of 27.56in (70cm) and adjustable mounting depth range of 19.5-38in, this shelf can work with any 19in cabinet or equipment rack. It provides additional storage space for your tools or A/V accessories.
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this adjustable rack shelf is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
U Height	1U
Cable Management	No

Performance

Weight Capacity (Stationary)	176.4 lb [80 kg]
---------------------------------	------------------

Special Notes / Requirements

Note	Depth adjustable from 19-38"
------	------------------------------

Physical Characteristics

Color	Black
Internal Width	17.6 in [44.6 cm]
Internal Height	1.6 in [40 mm]
Internal Depth	27.6 in [70 cm]
Product Length	38.3 in [97.4 cm]
Product Width	17.5 in [44.5 cm]
Product Height	1.6 in [4.0 cm]
Weight of Product	9.7 lb [4.4 kg]
Maximum Mounting Depth	38.3 in [97.4 cm]

Minimum Mounting Depth 19.5 in [49.5 cm]

Packaging Information

Package Quantity	1
Package Length	19.7 in [50.1 cm]
Package Width	32.4 in [82.3 cm]
Package Height	2.9 in [7.3 cm]
Shipping (Package) Weight	12.6 lb [5.7 kg]

What's in the Box

Included in Package	1 - slotted fixed shelf
	2 - front mounting brackets
	2 - rear mounting brackets
	8 - M5 screws
	8 - M5 cage nuts
	8 - M5 flanged lock nuts
	8 - M5 truss head screws
	1 - instruction manual

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*