

HAMMER Boost 2 LTE

The latest evolution of HAMMER’s **tough-and-trusted** feature phone line. **Boost 2 LTE** combines compact design with serious durability, meeting **IP68** and **MIL-STD-810H** standards.

Equipped with a **2.4” IPS display**, large tactile keys and a loudspeaker, it’s built for work and the outdoors.

A replaceable **3500 mAh battery** delivers up to 25 days of standby, while **4G LTE** with **VoLTE** and **Dual SIM** keep you connected.

Additional features include Bluetooth 5.1, **USB-C charging**, **FM radio**, and a **bright LED torch** — all in a **rugged**, portable body.



Water and dust resistance



MIL-STD-810H



2 MP



3,500 mAh

Camera	2MP	Processor	Unisoc T127
Resistance	IP68, Drop test 1.5M	Battery	3,500mAh
Display	2.4” IPS	Dual SIM	Yes, Stand by
Memory	64MB + 128MB	Weight & Dimensions	137.2 x 64.9 x 22.5, 241g