

HAMMER 6 LTE



A new icon of **rugged** reliability. The HAMMER 6 LTE delivers **military-grade durability** (IP68, MIL-STD-810H, 1.5 m drop test), a 2.4" IPS screen, and an **SOS button** for peace of mind.

Powered by a **2500 mAh** replaceable battery for up to 7 days standby or 10 hours talk time, it also offers clear **4G LTE** with **VoLTE** and **Dual SIM** flexibility.

Enhanced usability features include large backlit keys, a practical side-mounted torch, **FM radio**, and **USB-C charging**—all wrapped in a **reinforced**, no-nonsense design.



Water and dust resistance



MIL-STD-810H



2 MP



2,500 mAh

Camera	2MP	Processor	Unisoc T107
Resistance	IP68, Drop test 1.5M	Battery	2,500mAh
Display	2.4" IPS	Dual SIM	Yes, Stand by
Memory	48MB + 128MB	Weight & Dimensions	132 x 60 x 18, 163g