

PLOT 100VF

100 W Mini Fresnel light with variable white

The Centolight **PLOT 100VF** is a versatile two-color COB Fresnel projector, ideal for stage lighting, photography, videography, theatre and event setups. Equipped with a powerful 100W LED-source offering both Warm and Cold White options, it enables seamless blending of color temperatures to match diverse environments and artistic requirements. The fixture features multiple control modes, including Sound Control, DMX512, Master-Slave, and Automatic, along with a variable strobe effect and linear dimming, ensuring maximum flexibility for various applications. With two DMX channel configurations available, users can make precise lighting adjustments. Delivering energy-efficient, high-brightness illumination with uniform coverage, the **PLOT 100VF** is perfectly suited for dynamic and professional lighting scenarios.



PRODUCT DETAILS

Key features

Two-color COB Fresnel projector

100W LED source

Electronic strobe with variable speed

Smooth dimming function

White color temperature variation Warm and Cold White

Stand-alone, Master/Slave, DMX512 and Sound Control modes

Specifications

Input Voltage	AC90-240V, 50-60Hz
LED	100W Warm and Cold White COB
Lens	Fresnel
DMX Channels	2 - 6CH Modes
Control Mode	DMX, Master/Slave, Auto, Sound
DMX Connectors	3-pin XLR Input/Output
Power Connectors	Powercon Input
Fixture Dimensions (WxDxH)	127,5 x 177 x 125 mm(5.02 x 6.97 x 4.92 in.)
Dimensions with bracket and screw knobs (WxDxH)	169 x 177 x 198.5(6.65 x 6.97 x 7.81 in.)
Packing Dimensions (WxDxH)	190 x 190 x 220 mm(7.48 x 7.48 x 8.66 in.)
Product Weight	1.66 kg – 3.66 lbs.
Package Weight	2.5 kg – 5.5 lbs