



PRODUCT SPEC SHEET

SKU 212651

Model:VT-COB 512-N

EAN:3800157679640

VT-COB 512 13W/M LED COB STRIP LIGHT 6000K IP20 24V (5M/ROLL)(PRICE PER M)



IP20
STANDARD

03
YEAR
WARRANTY



- Stable COB technology for better reliability and longer lifespan
- 5M Roll quantity
- CRI>90 witness true to life colors
- IP20 Ingress protection
- Suitable for illuminating borders, edges, cabinets, bars and areas with limited space for installation

TECHNICAL INFORMATION

Dimmable:	No
Model:	VT-COB 512-N
Color Temperature:	6500K
Watts per meter:	13
Current per meter:	0.54A
Lumens per meter:	1200
CRI:	>90
Input Power:	DC:24V
Color for Web:	White
Dimension:	10mm
LED Chip Type:	COB
Beam Angle:	120°
Energy Rating Label:	F (2021)
Roll Qty:	5M
IP Rating:	IP20

LISTING DETAILS

SKU:	212651
Model:	VT-COB 512-N
EAN:	3800157679640
Commodity Code:	94054940

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000187
Dimension:	10mm

MASTER BOX PACKAGING

Box Qty:	400
Qty Per Pallet:	8000
Length (Box) mm:	10
Width (Box) mm:	200

