



PRODUCT SPEC SHEET

SKU 10555

Model:VT-COB 560

EAN:3800170208957

VT-COB 560 18W LED COB STRIP LIGHT WITH CCT IP20 24V



IP20
STANDARD

- Stable COB technology for better reliability and longer lifespan
- 5M Roll quantity
- CRI>90 witness true to life colors
- IP20 Ingress protection
- Compatible with SKU 2901 infrared controller for CCT functioning (To be bought separately)
- Suitable for illuminating borders, edges, cabinets, bars and areas with limited space for installation

TECHNICAL INFORMATION

No. Of Led:	560
Model:	VT-COB 560
Color Temperature:	3IN1
Watts per meter:	18
Lumens per meter:	1135
CRI:	>90
Input Power:	DC:24V
Color for Web:	3IN1
Dimension:	8mm
LED Chip Type:	COB
Beam Angle:	120°
Energy Rating Label:	G (2021)
Roll Qty:	5M
IP Rating:	IP20

LISTING DETAILS

SKU:	10555
Model:	VT-COB 560
EAN:	3800170208957
Commodity Code:	94054231

PACKAGING

Gross Weight (Kgs):	0.03
Unit CBM:	0.000147
Dimension:	8mm

MASTER BOX PACKAGING

Box Qty:	400
Qty Per Pallet:	12000
Length (Box) mm:	180

Width (Box) mm:	10
Height (Box) mm:	200