



PRODUCT SPEC SHEET

SKU 23141

Model:VT-COB 320

EAN:3800170211216

VT-COB 320 10W LED COB STRIP LIGHT RED IP67 24V



IP67 STANDARD

- Stable COB technology for better reliability and longer lifespan
- 5M Roll quantity
- CRI>80 witness true to life colors
- IP67 Ingress protection
- Suitable for illuminating borders, edges, cabinets, bars and areas with limited space for installation

TECHNICAL INFORMATION

Model:	VT-COB 320
Color Temperature:	Red
Watts per meter:	10
Lumens per meter:	840
CRI:	>80
Color for Web:	RED
Dimension:	8mm
LED Chip Type:	COB
Beam Angle:	120°
Roll Qty:	5M
IP Rating:	IP67

LISTING DETAILS

SKU:	23141
Model:	VT-COB 320
EAN:	3800170211216
Commodity Code:	94054231

PACKAGING

Gross Weight (Kgs):	0.08
Unit CBM:	0.00031
Dimension:	8mm

MASTER BOX PACKAGING

Box Qty:	400
Qty Per Pallet:	4800
Length (Box) mm:	230
Width (Box) mm:	230

