



PRODUCT SPEC SHEET

SKU 23858

Model:VT-4909

EAN:3800170229075

VT-4909 10W LED PIR SENSOR FLOODLIGHT 1M WIRE 3000K BLACK BODY 120LM/W



IP65
STANDARD

02 YEAR
WARRANTY

Super Bright
120
LUMENS/W

- High quality Slim series Floodlight with PIR Sensor and 1 Meter Wire
- Designed with high efficiency SMD Chips
- Powerful LED light source with high lumen efficiency of 120 LM/W
- 3-8m (Radius) Detection Distance
- Built Strong and durable with Aluminium - Corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more

TECHNICAL INFORMATION

Dimmable:	No
Time Delay:	Min 7sec+2sec Max 7min+2min
Detection Range:	120°±20°
Instant Start:	0-100% in <1s
Model:	VT-4909
Color Temperature:	3000K
Detection Distance:	3-8m (Radius)
CRI:	>70
Watts:	10
Lumens:	1200
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	Black
Color for Web:	Warm White
Body Type:	Aluminium

LISTING DETAILS

SKU:	23858
Model:	VT-4909
EAN:	3800170229075
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	0.49
Unit CBM:	0.0021
Dimension:	152.5x88.3x182.8mm

MASTER BOX PACKAGING

Box Qty:	20
Qty Per Pallet:	
Length (Box) mm:	156

Dimension:	152.5x88.3x182.8mm
Operation Temperature:	-20°C to +45°C
PF:	>0.7
LED Chip Type:	SMD
Beam Angle:	120°
Energy Rating Label:	E (2021)
Sensor Type:	PIR
Wire Length:	1m
Energy Saving:	85 Energy
IP Rating:	IP65
IK Rating:	IK05
Long Life:	25,000 Hours
lumens per watt:	120

Width (Box) mm:	63
Height (Box) mm:	175