



# PRODUCT SPEC SHEET

**SKU 23860**

Model:VT-4909

EAN:3800170229099

## VT-4909 10W LED PIR SENSOR FLOODLIGHT 1M WIRE 6500K BLACK BODY 120LM/W



- High quality Slim series Floodlight with PIR Sensor and 1 Meter Wire
- Designed with high efficiency SMD Chips
- Powerful LED light source with high lumen efficiency of 120 LM/W
- 3-8m (Radius) Detection Distance
- Built Strong and durable with Aluminium - Corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more

## TECHNICAL INFORMATION

<b>Dimmable:</b>	No
<b>Time Delay:</b>	Min 7sec+2sec Max 7min+2min
<b>Detection Range:</b>	120°±20°
<b>Instant Start:</b>	0-100% in <1s
<b>Model:</b>	VT-4909
<b>Color Temperature:</b>	6500K
<b>Detection Distance:</b>	3-8m (Radius)
<b>CRI:</b>	>70
<b>Watts:</b>	10
<b>Lumens:</b>	1200
<b>Input Power:</b>	AC:220-240V, 50/60Hz
<b>Unit Color:</b>	Black
<b>Color for Web:</b>	White
<b>Body Type:</b>	Aluminium

## LISTING DETAILS

<b>SKU:</b>	23860
<b>Model:</b>	VT-4909
<b>EAN:</b>	3800170229099
<b>Commodity Code:</b>	94054210

## PACKAGING

<b>Gross Weight (Kgs):</b>	0.5
<b>Unit CBM:</b>	0.00214
<b>Dimension:</b>	152.5x88.3x182.8mm

## MASTER BOX PACKAGING

<b>Box Qty:</b>	20
<b>Qty Per Pallet:</b>	
<b>Length (Box) mm:</b>	156

<b>Dimension:</b>	152.5x88.3x182.8mm
<b>Operation Temperature:</b>	-20°C to +45°C
<b>PF:</b>	>0.7
<b>LED Chip Type:</b>	SMD
<b>Beam Angle:</b>	120°
<b>Energy Rating Label:</b>	E (2021)
<b>Sensor Type:</b>	PIR
<b>Wire Length:</b>	1m
<b>Energy Saving:</b>	85 Energy
<b>IP Rating:</b>	IP65
<b>IK Rating:</b>	IK05
<b>Long Life:</b>	25,000 Hours
<b>lumens per watt:</b>	120

<b>Width (Box) mm:</b>	63
<b>Height (Box) mm:</b>	175