



PRODUCT SPEC SHEET

SKU 23865

Model:VT-4929

EAN:3800170229143

VT-4929 30W LED PIR SENSOR FLOODLIGHT 1M WIRE 4000K BLACK BODY 120LM/W



IP65
STANDARD

02 YEAR
WARRANTY

Super Bright
120
LUMENS/W

- Slim series PIR Sensor Floodlight with 1 Meter wire
- High quality LED SMD chip and high power driver
- Powerful LED light source with lumen efficiency of 120 LM/W
- Detects motion within a radius of 3 to 8 Meter
- Installing Height 1.8 Meter to 2.5 Meter
- Built Strong and durable with an Aluminium Body and a corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more

TECHNICAL INFORMATION

| | |
|---------------------|--------------------------------|
| Dimmable: | No |
| Time Delay: | Min 7sec+2sec Max 7min+2min |
| Detection Range: | 120°±20° |
| Instant Start: | 0-100% in <1s |
| Model: | VT-4929 |
| Color Temperature: | 4000K |
| Detection Distance: | 3-8m (Radius) |
| CRI: | >70 |
| Watts: | 30 |
| Lumens: | 3600 |
| Input Power: | AC:220-240V, 50Hz |
| Unit Color: | Black |
| Color for Web: | Day White |

LISTING DETAILS

| | |
|-----------------|---------------|
| SKU: | 23865 |
| Model: | VT-4929 |
| EAN: | 3800170229143 |
| Commodity Code: | 9405429000 |

PACKAGING

| | |
|---------------------|--------------------|
| Gross Weight (Kgs): | 0.48 |
| Unit CBM: | 0.003066 |
| Dimension: | 224.3x184.5x88.3mm |

MASTER BOX PACKAGING

| | |
|------------------|-----|
| Box Qty: | 20 |
| Qty Per Pallet: | |
| Length (Box) mm: | 188 |

| | |
|------------------------|--------------------|
| Body Type: | Aluminium |
| Dimension: | 224.3x184.5x88.3mm |
| Operation Temperature: | -20°C to +45°C |
| PF: | >0.9 |
| LED Chip Type: | SMD |
| Beam Angle: | 120° |
| Energy Rating Label: | E (2021) |
| Sensor Type: | PIR |
| Wire Length: | 1m |
| Energy Saving: | 85 Energy |
| IP Rating: | IP65 |
| IK Rating: | IK05 |
| Long Life: | 25,000 Hours |
| lumens per watt: | 120 |

| | |
|------------------|-----|
| Width (Box) mm: | 63 |
| Height (Box) mm: | 217 |