



PRODUCT SPEC SHEET

SKU 76841

Model:VT-702CL-C

EAN:3800170217935

VT-702CL-C CANLESS FIRE RATED GU10 FITTING IP65 CHROME BEZEL



IP65
STANDARD

03
YEAR
WARRANTY

- Twist & lock fire rated canless fitting designed with GU10 base(*lamp not included)
- Fire-rated to resistance of 30,60,90 Mins
- Elegant Black+Chrome color finish
- Easy connection - Quick Connector included
- Insulation Cover available(*not included)
- Spring clips for safer installation and easy maintenance
- IP65 rated protection
- Suitable for residential and commercial installations

TECHNICAL INFORMATION

Cutting Size:	75 mm
Model:	VT-702CL-C
Installation Type:	Recessed
Input Power:	AC:200-240V, 50Hz
Unit Color:	Black+Chrome
Body Type:	Pressed Steel
Dimension:	91x70mm
Base:	GU10
Shape:	Round
IP Rating:	IP65

LISTING DETAILS

SKU:	76841
Model:	VT-702CL-C
EAN:	3800170217935
Commodity Code:	9405110000

PACKAGING

Gross Weight (Kgs):	0.25
Unit CBM:	0.001178
Dimension:	91x70mm

MASTER BOX PACKAGING

Box Qty:	100
Qty Per Pallet:	
Length (Box) mm:	120

Width (Box) mm:

105

Height (Box) mm:

85