



PRODUCT SPEC SHEET

SKU 23736

Model:VT-9-154

EAN:3800170226906

VT-9-154 150W/120W/80W LED HIGHBAY SOSEN DRIVER 1M WIRE 90° 4000K



IP65
STANDARD

05
YEAR
WARRANTY

Super Bright
210
LUMENS/W



- Powerful LED light source with lumen efficiency of 210 LM/W
- Watts Changeable option 80W/120W/150W
- Lasts 50,000 Hours, longer life span than Standard Highbays
- IK08 Rated
- Designed with SOSEN driver and 1 meter wire
- 110° and 60° lens options(To be bought separately)
- Dimmable Microwave & PIR sensor, Remote Control & Adjustable bracket installation kit(To be bought separately)
- Suitable for industrial usage, warehouses, supermarkets, workshops, factories, warehouses, highways, toll stations, gas stations, malls, exhibition halls, and stadiums

TECHNICAL INFORMATION

On/Off Cycles:	>15000
Model:	VT-9-154
Color Temperature:	4000K
CRI:	>80
Watts:	150
Lumens:	31500
Useful Lumens:	27000
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	Black
Color for Web:	Day White
Body Type:	Aluminium
Dimension:	250x110mm
PF:	>0.9

LISTING DETAILS

SKU:	23736
Model:	VT-9-154
EAN:	3800170226906
Commodity Code:	9405429000

PACKAGING

Gross Weight (Kgs):	1.96
Unit CBM:	0.0102
Dimension:	250x110mm

MASTER BOX PACKAGING

Box Qty:	1
Qty Per Pallet:	

LED Chip Type:	SMD
Beam Angle:	90°
Energy Rating Label:	A (2021)
Driver Brand:	SOSEN
Wire Length:	1m
IP Rating:	IP65
IK Rating:	IK08
Long Life:	50,000 Hours
lumens per watt:	210

Length (Box) mm:	260
Width (Box) mm:	260
Height (Box) mm:	130