



PRODUCT SPEC SHEET

SKU 216392

Model:VT-6072-N

EAN:3800157687201

VT-6072 9W T8 LED PLASTIC TUBE NON ROTATABLE 60CM 3000K G13



IP20
STANDARD

03
YEAR
WARRANTY

- Nano-plastic tube offers better light transmittance
- Higher endurance and longevity compared to PC and glass
- Cost effective, safe retrofit for T8 Tubes
- Fitted with high efficiency SMD LED Chips
- Super thermal conductivity - Constant current integrated IC driver
- Wide light angle effectively diffuses glare
- Suitable for domestic and commercial lighting, offices, supermarkets, shops, hotels and many more

TECHNICAL INFORMATION

Dimmable:	No
On/Off Cycles:	>15000
Instant Start:	0-100% in < 1s
Model:	VT-6072-N
Color Temperature:	3000K
CRI:	>80
Watts:	9
Lumens:	850
Input Power:	AC:220-240V,50Hz
Unit Color:	White
Color for Web:	Warm White
Body Type:	Nano Plastic
Dimension:	600x28mm

LISTING DETAILS

SKU:	216392
Model:	VT-6072-N
EAN:	3800157687201
Commodity Code:	8539520000

PACKAGING

Gross Weight (Kgs):	0.1
Unit CBM:	0.000706
Dimension:	600x28mm

MASTER BOX PACKAGING

Box Qty:	25
Qty Per Pallet:	2100
Length (Box) mm:	653

Operation Temperature:	-20°C to +45°C
Base:	G13
Shape:	T8
PF:	>0.5
LED Chip Type:	SMD
Beam Angle:	160°
Downward LOR (%):	70.1
ULR (%):	29.9
Energy Rating Label:	F (2021)
IP Rating:	IP20
Long Life:	25,000 Hours
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate

Width (Box) mm:	29
Height (Box) mm:	29