



PRODUCT SPEC SHEET

SKU 216394

Model:VT-6072-N

EAN:3800157687225

VT-6072 9W T8 LED PLASTIC TUBE NON ROTATABLE 60CM 6500K G13



IP20
STANDARD

03
YEAR
WARRANTY

- Nano-plastic tube offers better light transmittance
- Higher endurance and longevity compared to PC and glass
- Cost effective, safe retrofit for T8 Tubes
- Fitted with high efficiency SMD LED Chips
- Super thermal conductivity - Constant current integrated IC driver
- Wide light angle effectively diffuses glare
- Suitable for domestic and commercial lighting, offices, supermarkets, shops, hotels and many more

TECHNICAL INFORMATION

Dimmable:	No
On/Off Cycles:	>15000
Instant Start:	0-100% in < 1s
Model:	VT-6072-N
Color Temperature:	6500K
CRI:	>80
Watts:	9
Lumens:	850
Input Power:	AC:220-240V,50Hz
Unit Color:	White
Color for Web:	White
Body Type:	Nano Plastic
Dimension:	600x28mm

LISTING DETAILS

SKU:	216394
Model:	VT-6072-N
EAN:	3800157687225
Commodity Code:	8539520000

PACKAGING

Gross Weight (Kgs):	0.1
Unit CBM:	0.000707
Dimension:	600x28mm

MASTER BOX PACKAGING

Box Qty:	25
Qty Per Pallet:	2100
Length (Box) mm:	653

Operation Temperature: -20°C to +45°C

Base: G13

Shape: T8

PF: >0.5

LED Chip Type: SMD

Beam Angle: 160°

Downward LOR (%): 70.0

ULR (%): 30.0

Energy Rating Label: F (2021)

IP Rating: IP20

Long Life: 25,000 Hours

EMC Certificate: [Check the certificate](#)

LVD Certificate: [Check the certificate](#)

ROHS Certificate: [Check the certificate](#)

Width (Box) mm: 29

Height (Box) mm: 29