



PRODUCT SPEC SHEET

SKU 216310

Model:VT-1577-N

EAN:3800157687263

VT-1577 20W T8 LED PLASTIC TUBE NON ROTATABLE 150CM 6500K G13



IP20
STANDARD

03
YEAR
WARRANTY

- Nano-plastic tube offers better light transmittance
- Higher endurance and longevity compared to PC and glass
- Cost effective, safe retrofit for T8 Tubes
- Fitted with high efficiency SMD LED Chips
- Super thermal conductivity - Constant current integrated IC driver
- Wide light angle effectively diffuses glare
- Suitable for domestic and commercial lighting, offices, supermarkets, shops, hotels and many more

TECHNICAL INFORMATION

Dimmable:	No
On/Off Cycles:	>15000
Instant Start:	0-100% in < 1s
Model:	VT-1577-N
Color Temperature:	6500K
CRI:	>80
Watts:	20
Lumens:	2100
Input Power:	AC:220-240V,50Hz
Unit Color:	White
Color for Web:	White
Body Type:	Nano Plastic
Dimension:	1500x28mm

LISTING DETAILS

SKU:	216310
Model:	VT-1577-N
EAN:	3800157687263
Commodity Code:	8539520000

PACKAGING

Gross Weight (Kgs):	0.21
Unit CBM:	0.001663
Dimension:	1500x28mm

MASTER BOX PACKAGING

Box Qty:	25
Qty Per Pallet:	700
Length (Box) mm:	1558

Operation Temperature:	-20°C to +45°C
Base:	G13
Shape:	T8
PF:	>0.7
LED Chip Type:	SMD
Beam Angle:	160°
Downward LOR (%):	69.1
ULR (%):	30.9
Energy Rating Label:	F (2021)
IP Rating:	IP20
Long Life:	25,000 Hours
lumens per watt:	105
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate

Width (Box) mm:	29
Height (Box) mm:	29