



PRODUCT SPEC SHEET

SKU 2142151

Model:VT-1855-N

EAN:3800157682558

VT-1855 4.5W LED CANDLE BULB 3000K E14



IP20
STANDARD

02 YEAR
WARRANTY

- Modern LED SMD technology for better reliability and durability
- Replaces 40 watts old halogen lamp
- Lasts 20,000 Hours, longer life span than Standard halogen lamps
- Designed for E14 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

TECHNICAL INFORMATION

Inner Box Qty:	10
On/Off Cycles:	>20000
Model:	VT-1855-N
Color Temperature:	3000K
CRI:	>80
Watts:	4.5
Lumens:	470
Input Power:	AC:220-240V, 50Hz
Equivalence Watts:	40
Unit Color:	White
Color for Web:	Warm White
Body Type:	Thermoplastic
Dimension:	36.5x100mm
Operation Temperature:	-20°C to +45°C
Base:	E14

LISTING DETAILS

SKU:	2142151
Model:	VT-1855-N
EAN:	3800157682558
Commodity Code:	85395200

PACKAGING

Gross Weight (Kgs):	0.02
Unit CBM:	0.000198
Dimension:	36.5x100mm

MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	7000
Length (Box) mm:	39
Width (Box) mm:	39
Height (Box) mm:	102

Shape:	Candle
PF:	>0.5
LED Chip Type:	SMD
Beam Angle:	180°
Energy Rating Label:	F (2021)
Energy Saving:	80 Energy
IP Rating:	IP20
Long Life:	20,000 Hours
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate